

Device Boxes

Conduit Knockouts



CI425

"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



BC1102

Recessed ears.



CI1102-SB



CI3102-SSX

"Wraparound" bracket for 1-5/8 in. steel studs. With integral support bracket.



BC1104

Recessed ears.



CI1104-B



Cat. No.	Volume (Cu. in.)	Features		Knockouts	
		Ears	Bracket	1/2 in. ends	1/2 in. bottom
2 in. Deep — Gangable — 3 in. x 2 in.					
C1425	10.0	flush	rework	2	-
BC1102	10.0	recessed	-	2	-
CI1102-SB	10.0	-	"SB"	2	-
Cl3102-SSX	12.0	-	"SSX"	2	-
2-1/2 in. Deep — Gangable — 3 in. x 2 in.					
BC1104	12.5	recessed	-	2	2
CI1104-B	12.5	-	"B"	2	2