

Bar Hangers and Brackets



BC1041 / BC1042



6010-DW-25 / 6010-ADW-25



6011-DW-25 / 6011-ADW-25









O-t N-	Description
Cat. No.	Description
Bar Hangers	
BC1041	Adjustable from 11-1/2 in. to 18-1/2 in. Maximum load capacity: 50 lb. (22.7)
BC1042	Adjustable from 16-1/2 in. to 26-1/2 in. When extended up to 22-1/2" 50 lb. (22.7). When extended up to 26-1/2 in. 25 lb. (11.35)
Adjustable Bar Hangers for Plaster and Drywall — Depth 1-3/16 in.	
6010-DW-25 [†]	For 3/8 in., 1/2 in. and 5/8 in. wall board and plaster. Score marks for drywall and plaster depths. Maximum load capacity: 50 lb. (22.7). Length: 10-1/2 in. to 18-1/2 in. Packaged complete with stud
6010-ADW-25 [†]	For 3/8 in., 1/2 in. and 5/8 in. wall board and plaster. Score marks for drywall and plaster depths. Maximum load capacity: 50 lb. (22.7). Length: 14-1/2 in. to 26-1/2 in. Packaged complete with stud
6011-DW-25 [†]	For 3/8 in., 1/2 in. and 5/8 in. wall board and plaster. Score marks for drywall and plaster depths. Maximum load capacity: 50 lb. (22.7). Length: 10-1/2 in. to 18-1/2 in. Packaged complete with fastener
6011-ADW-25 [†]	For 3/8 in., 1/2 in. and 5/8 in. wall board and plaster. Score marks for drywall and plaster depths. Maximum load capacity: 50 lb. (22.7). Length: 14-1/2 in. to 26-1/2 in. Packaged complete with fastener
Support Brackets	
CI1060	Length: 16 in. Grooved for box ears