

# **Device Boxes**

## **Armoured and Nonmetallic Sheathed Cable Clamps**



#### CI3102-LSSAX

"Wraparound" bracket for 1-5/8 in. steel studs. With integral support bracket.



BC1104-LA

Flush ears.



#### BC1104-LHA

Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.



CI1104-LMSA

Mounting strap recessed 1/2 in.



**BC1104-LSSAX** 



### CI3004-LSSAX-1

1 in. recessed brackets for 2-1/2 in. and 3-5/8 in. steel studs. **Brackets positioned for 2 layers of 1/2 in.** drywall.



Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
2 in. Deep — Gangable — 3 in. x 2 in.				
CI3102-LSSAX	12.0	-	"SSX"	4
2-1/2 in. Deep — Gangable — 3 in. x 2 in.				
BC1104-LA	12.5	flush	-	4
BC1104-LHA	12.5	-	P. Tabs	4
CI1104-LMSA	12.5	-	"MS"	4
BC1104-LSSAX	12.5	-	"SSX"	4
3 in. Deep — Gangable — 3 in. x 2 in.				
Cl3004-LSSAX-1*	18.0	-	"SSX"	4

<sup>\*</sup> Brackets positioned for 2 layers of 5/8 in. drywall





