

## **Device Boxes**

## **Armoured and Nonmetallic Sheathed Cable Clamps**



Flush ears.



**BC775-LD** 

"Swing-arm" rework brackets. Max. wall thickness: 3/4 in.



BC777-LRB

Pivoting ends for rework installation. Max. wall thickness: 1-1/8 in. Non-Gangable

BC1104-LSSX



CI525-I

"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



**CI1104-LMS** 

Mounting strap with prongs. Recessed 1/2 in.



One screw mounting Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.



BC1104-LB



BC1104-L

Flush ears.



**BC1104-LRB** Flat sides for rework applications.



**BC1104-LRW** Rework bracket for closed wall applications. Max. wall thickness: 1 in.

**BC1104-LHT** 

Positioning tabs. Provision for external

nailing. Two embossed mounting slots for internal screw installation.



