

Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps



BC1100-L

Flush ears.



BC1100-LLE

Less ears.



CI1100-LRE

Recessed ears.



CI425-L

"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.



BC1102-L

Flush ears.



BC1102-LH

Provision for external nailing.



Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
1-1/2 in. Deep — Gangable — 3 in. x 2 in.				
BC1100-L	8.0	flush	-	4
BC1100-LLE	8.0	-	-	4
CI1100-LRE	8.0	recessed	-	4
2-1/2 in. Deep — Gangable — 3 in. x 2 in.				
Cl425-L	10.0	flush	rework	4
BC1102-L	10.0	flush	-	4
BC1102-LH	10.0	-	-	4