

## Cable Ties



Std. Pkg. Cat. No.	Body Width (in./mm)	Length (in./mm)	Max. Wire Bundle Dia. (in./mm)	Tensile Strength (lb./N)	Std. Pkg.
<b>Ty-Rap® Nylon 6/6 Cable Tie – Colour Assortment</b>					
<b>TY525M-CLRS</b>	0.19/4.83	7.31/185.67	1.75/44.45	50/222.40	10

Cable ties are same size as TY525M shown above. 10 ties in each colour (black, brown, red, orange, yellow, green, blue, purple, grey & white) are packaged. 100 total cable ties per package.

### The colours you need in convenient packs!

#### Ty-Rap® Nylon 6.6 Cable Ties – Colour Assortment

- Construction – nylon 6.6, 316 stainless steel locking device



Std. Cat. No.	Bulk Cat. No.	Description	Length (in./mm)	Tensile Strength (lb./N)	Bulk Pkg.
-	<b>TY525M-CLRS</b>	Multi-Coloured Natural Nylon (10 each of standard ten colours)	7.31/185.67	50/222.40	100 ties
-	<b>TY25M-0</b>	Black, Natural Nylon			1,000 Ties
-	<b>TY25M-1</b>	Brown, Natural Nylon			
-	<b>TY25M-2</b>	Red, Natural Nylon			
-	<b>TY25M-3</b>	Orange, Natural Nylon			
-	<b>TY25M-4</b>	Yellow, Natural Nylon			
-	<b>TY25M-5</b>	Green, Natural Nylon			
-	<b>TY25M-6</b>	Blue, Natural Nylon			
-	<b>TY25M-7</b>	Purple, Natural Nylon			
-	<b>TY25M-8</b>	Grey, Natural Nylon			
-	<b>TY25M-9</b>	White, Natural Nylon			

For use in temperatures ranging from -40°F to 185°F (-40°C to 85°C)

- UL Listed Natural 6.6 Nylon Cable Ties are suitable for use in air handling spaces (plenums) in accordance with Section 300.22 (C) & (D) of the National Electrical Code
- 100 standard ties in black, brown, red, orange, yellow, green, blue, purple, grey and white (10 each)
- Recommended tooling – ERG-50, WT1-TB

Natural nylon is standard. For coloured Ty-Rap® ties, add the following suffix numbers to catalogue numbers.  
**Example:** TY25M-2 would be red TY25M. (Consult Regional Sales Office for ordering information.)

**How to Order Coloured Ty-Rap® Cable Ties and Accessories**

Colour	Suffix No.	Colour	Suffix No.	Colour	Suffix No.	Colour	Suffix No.
Black	X	Red	2	Green	5	Grey	8
(outdoor)		Orange	3	Blue	6	White	9
Brown	1	Yellow	4	Purple	7		