



METER SOCKET • 400 AMP. 120/240 VOLTS • SINGLE PHASE SERVICE





Dimensions are in inches

- Permanent red nameplate affixed to front cover warns that removal of meter does not isolate the load terminals; also notice of automatic circuit closing device on JS4A and warning to short circuit current transformer secondary before removal of meter on JS4B
- Meter socket configuration for 5 jaw meters (can be readily converted to suit meter forms requiring 4 blades)
- 400/5 AMP. three-wire current transformer provides low current for service metering proportional to higher current draw. Consumer and Corporate Affairs Canada approved for revenue metering (200/5 and 300/5 AMP. also available)
- Gutter wiring space provided on left side
- Twin covers allow access to either compartment (single cover available on request)
- Hub opening closure plate for underground service. All units can be converted to overhead service with addition of conduit hub and JS250 or JS500 tunnel type connector kit.
- Line side terminations: double 1/2" studs to accommodate compression lugs for underground service (1 x 500 kcmil or 2 x 250 kcmil)
- Hinged bridges and readily removable crossbar with keyholes permit easy wiring without obstructions
- Load side terminations: tunnel type connectors, dual rated for 1 x 500 kcmil or 2 x 250 kcmil
- · Fully wired secondary circuits
- 30-5/8" H x 20-1/4" W x 8-3/8" D heavy gauge galvanized steel. Ovencured grey enamel finish.
 Weight each: 72 lb / 32.7 kg
- For aluminum JS4's see page 32 for product specs and dimensions
- Three 1-1/4", 1-1/2", 2", 2-1/2", 3", 3-1/2", 4" Bottom Knockouts
- Weatherproof type 3R enclosure


PRODUCT USAGE BY PROVINCE / UTILITY						
NFLD	JS4B-4ST	Sask.	JS4A-4TWE	Northern Ont.	JS4A, JS4A-4	
Que.	None approved	AB	JS4B-4T	Cornwall Hydro	JS4A-4T, JS4AB-4TW	
N.S.	WS, EAL, JS4B-STNS	B.C.	JS4B-4STW	Ottawa Hydro	JS4AB-TW	
N.B.	JS4B (EAL)	Hydro	JS4A, JS4A-200/5, JS4A-300/5, JS4A-4, JS4A-4T, JS4B, JS4B-4			
Man.	JS4A-4TW, JS4A-TWK, EAL	Ont.	JS4B-ST, JS4AB, JS4A5			



JS4 Series




METER SOCKET • 400 AMP. 120/240 VOLTS • SINGLE PHASE SERVICE





1 x 500 kcmil



1 x 500 kcmil

2 x 250 kcmil

2 x 250 kcmil with kit no. JS500 with kit no. JS250

UNDERGROUND SERVICE

OVERHEAD SERVICE

Ordering Information

CATALOGUE NUMBER	JS4 UNDERGROUND 400 TO 5 RATIO • 5 JAW • TWIN COVER			
JS4A	Equipped with automatic circuit closing device			
JS4B	Equipped with test switches			
INCLUDE	FACTORY MODIFICATIONS			
-4	4 jaw meter socket configuration			
-S	Provision only for test switches (test switches supplied by power authority)			
-T	Provision only for current transformer (transformer supplied by power authority)			
-W	Secondary circuit wiring not included (secondary circuit wired by power authority)			
-Z	"Peerless security" collar			
-200 / 5	200 to 5 ratio current transformer			
-300 / 5	300 to 5 ratio current transformer			
CATALOGUE NUMBER	OVERHEAD ENTRY CONVERSION KITS (1 KIT REQUIRED PER SOCKET)			
JS250	2 x 250 kcmil tunnel connector kit for line side terminations			
JS500	1 x 500 kcmil tunnel connector kit for line side terminations			
KIT-JS4B	5 th jaw assembly kit for NB Power			

NOTE: Refer to p.36 for "Product usage by Province utility"



Approved for copper or aluminum.