









Manual Motor Protector MS325

	Thermal setting range (Amps)			3-phase horsepower ratings			Catalog Number
	240V	480V	600V	240V	480V	600V	
 MS325	0.10 - 0.16	-	-	-	-	-	MS325-0.16
	0.16 - 0.25	-	-	-	-	-	MS325-0.25
	0.25 - 0.40	-	-	-	-	-	MS325-0.40
	0.40 - 0.63	-	-	-	-	-	MS325-0.63
	0.63 - 1.0	-	1/2	1/2	1/2	1/2	MS325-1.0
UL 580 Type E	1.0 - 1.6	-	3/4	3/4	3/4	3/4	MS325-1.6
	1.6 - 2.5	1/2	1	1.5	1.5	1.5	MS325-2.5
	2.5 - 4.0	1	2	3	3	3	MS325-4.0
	4.0 - 6.3	1.5	3	5	5	5	MS325-6.3
	6.3 - 9.0	2.5	5	7.5	7.5	7.5	MS325-9.0
MS325, BEA26/325, A26-30-10-84, S3-M3, CK-11	9.0 - 12.5	3	7.5	10	10	10	MS325-12.5
	12.5 - 16	5	10	10	10	10	MS325-16
	16 - 20	5	10	15	15	15	MS325-20
	20 - 25	7.5	15	20	20	20	MS325-25
ACCESSORIES FOR MS325							
	DESCRIPTION						Catalog Number
	1 NO & 1 NC Auxiliary contact blocks, side mount						MS325-HK11
	2 NO Auxiliary contact blocks, side mount						MS325-HK20
	2 NC Auxiliary contact blocks, side mount						MS325-HK02
 MS325-HK11	1 NO & 1 NC Auxiliary contact blocks, front mount						MS325-HKF11
	2 NO Auxiliary contact blocks, front mount						MS325-HKF20
 MS325-SK10	1 NO Bell alarm contact blocks						MS325-SK10
	1 NC Bell alarm contact blocks						MS325-SK01
 MS325-UA110	24VAC Undervoltage trip						MS325-UA24
	48VAC Undervoltage trip						MS325-UA48
	60VAC Undervoltage trip						MS325-UA60
	120VAC Undervoltage trip						MS325-UA110
	230VAC Undervoltage trip						MS325-UA230
	400VAC Undervoltage trip						MS325-UA400
	415VAC Undervoltage trip						MS325-UA415
	480VAC Undervoltage trip						MS325-UA480
 MS325-AS	110 - 240VAC/DC Shunt trip						MS325-ST110
	24 - 60VAC/DC Shunt trip						MS325-ST24
 BEA16/325	Busbar for direct mounting of contactors B6/B7						BEA7/325
	Busbar for direct mounting of reversing contactors VB6/VB7						MS325-VB7
	Busbar for direct mounting of contactors A9/A12/A16						BEA16/325
	Busbar for direct mounting of contactor A26						BEA26/325
 OTPA325B2P1	Gray Enclosure with black handle, IP64						OTPA325B2P1
	Gray Enclosure with red handle, IP64						OTPA325A2P1
	Gray Enclosure with clear cover, 4 poles, IP55						12644
	Gray Enclosure with clear cover, 6 poles, IP55						12646
	Line Side infeed block - required for UL508 type E						S3-M3
	Short circuit trip signal - required for UL 508 type E						CK-11