

# **Device Boxes**

## **Armoured and Nonmetallic Sheathed Cable Clamps**



#### BC1018-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



#### BC1304-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



#### BC2004-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



### BC2304-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



### BC2304-LHTQ-2

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



## BC2304-LHTQ-3

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs



## BC2304-LHTQ-4

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.



## BC3104-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.

Cat. No.	Dimensions H x W x D (in.)	Volume (Cu. in.)	Gangable Yes or No		Pryouts		
				One screw mounting	Pos. tabs	Prov. for external nailing	ends
BC1018-LHTQ	3 x 2 x 3	18.0	yes	yes	yes	yes	4
BC1304-LHTQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4
BC1304-LHATQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4
BC2004-LHTQ	3-3/4 x 2-3/16 x 2-3/4	20.5	no	yes	yes	yes	4
BC2304-LHTQ	3 x 2 x 2-1/2	14.5	no	yes	yes	yes	4
BC2304-LHTQ-2	3 x 3-3/4 x 2-1/2	27.0	no	yes	yes	yes	8
BC2304-LHTQ-3	3 x 5-1/2 x 2-1/2	39.5	no	no	yes	yes	12
BC2304-LHTQ-4	3 x 7-3/8 x 2-1/2	52.0	no	no	yes	yes	16
BC3104-LHTQ	3 x 2 x 2-1/2	16.0	yes	yes	yes	yes	4

# **Device Boxes**

# **Armoured and Nonmetallic Sheathed Cable Clamps**



BC2104-LLF

Holding prongs and prepositioned depth tabs.



BC2304-LHTQ

One screw mounting. Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.



BC2104-LX

Self-locking spring clamps. Holding prongs and prepositioned depth tabs. Raised ground screws. Approved for nonmetallic sheathed cable only.



BC2104-LN

Staked nails. Holding prongs and prepositioned depth tabs.



**BC2104-LRB** 

Flat sides for rework applications. 1 gang.



BC2104-LLE-2

2 gang. Holding prongs and prepositioned depth tabs.



BC2104-LRB-2

Flat sides for rework applications. 2 gang.



BC2104-LLE-3

 ${\bf 3}$  gang. Holding prongs and prepositioned depth tabs.



BC2104-LLE-4

 $4\ \mathrm{gang}.$  Holding prongs and prepositioned depth tabs.



BC2304-LHTQ-2

2 gang. Holding prongs and prepositioned



BC2304-LHTQ-3

3 gang. Holding prongs and prepositioned



BC2304-LHTQ-4

4 gang. Holding prongs and prepositioned



Cat. No.	Width	Volume (Cu. in.)	Features		Pryouts
Cat. No.	(in.)		Ears	Bracket	ends
2-1/2 in. Deep — Non-Gangable	— 3 in. High				
BC2104-LLE	2	12.5	-	P. Tabs	4
BC2104-LLE-2	3-3/4	25.0	-	P. Tabs	8
BC2104-LLE-3	5-1/2	37.5	-	P. Tabs	12
BC2104-LLE-4	7-3/8	50.0	-	P. Tabs	16
BC2104-LN	2	12.5	-	P. Tabs/Nails	4
BC2104-LX	2	12.5	-	P. Tabs	4
BC2304-LHTQ	2	14.5	-	P. Tabs	4
BC2304-LHTQ-2	3-3/4	27.0	-	P. Tabs	8
BC2304-LHTQ-3	5-1/2	39.5	-	P. Tabs	12
BC2304-LHTQ-4	7-3/8	52.0	-	P. Tabs	16
BC2104-LRB	2	12.5	-	-	4
BC2104-LRB-2	3-3/4	25.0	-	-	8