

Armoured Cable / Flexible Conduit

Accessories



CI5153

CI5154



| Cat. No. | Trade Size (in.) | | Clamping Range (in.) | |
|---|------------------|-------|----------------------|------|
| | EMT | Flex. | Min. | Max. |
| E.M.T / Flex. Couplings (Zinc Alloy) | | | | |
| CI5153 | 1/2 | 3/8 | 0.17 | 0.63 |
| CI5154 | | 1/2 | 0.75 | 0.95 |

CI0 / CI5

CIS-3 / CIS-4



| Cat. No. | Dimensions (in.) | | Hole Size (in.) | Suggested Application AC90 (BX) | Flex. Conduit (in.) |
|---|------------------|------|-----------------|------------------------------------|---------------------|
| | H | W | | | |
| Cable Straps (Aluminum) | | | | | |
| CI0 | 0.44 | 0.63 | 3/16 | 14/2 | — |
| CI1 | 0.50 | 0.56 | 3/16 | 12/2-10/2; 14/3-12/3; 14/4 | 5/16 |
| CI2 | 0.50 | 0.63 | 3/16 | 10/3; 12/4 | 3/8 |
| CI3 | 0.57 | 0.68 | 3/16 | 10/2; 10/3; 12/4 | — |
| CI4 | 0.81 | 1.06 | 3/16 | 6/2; 6/3; 8/4 | 1/2 |
| CI5 | 1.06 | 1.25 | 7/32 | 4/2-2/2; 4/3-2/3; 6/4-4/4 | 3/4 |
| Cable Staples (Galvanized Steel) | | | | | |
| CIS-3 | 0.49 | 0.70 | — | 14/2-12/2; 14/3-12/3 | 5/16 |
| CIS-4 | 0.76 | 0.86 | | 14/2-8/2; 14/3-8/3; 14/4-10/4 | 3/8, 7/16 |

CI38



| Cat. No. | Trade Size (in.) | Max. Flex. Conduit Dia. (in.) | Hole Size (in.) |
|--|------------------|-------------------------------|-----------------|
| Flexible Conduit Strap (Galvanized Steel) | | | |
| CI38 | 3/8 | 0.61 | 3/16 |

CI7538



| Cat. No. | Max. Flex. Conduit Dia. (in.) | Hole Size (in.) |
|---|-------------------------------|-----------------|
| One Hole Double Sided Strap (Galvanized Steel) | | |
| CI7538* | 1.05 | 3/16 |

*Any combination of 3/8 in., 1/2 in. and 3/4 in.
EMT, rigid conduit, flexible conduit or teck cables

EMT

Compression Fittings and Couplings

- All EMT compression connectors and couplings are concrete-tight
- Models from 2-1/2 to 4 in. are also suitable for rigid and IMC conduit



CI5604 (-IT) / CI5632 (-IT)



Steel Locknut
IT: with insulated throat

CI5804 (-IT) / CI5832 (-IT)



Zinc Die Cast Locknut
IT: with insulated throat

| Cat. No. | | | | Trade Size (in.) |
|---------------------------------|-----------|---------|-----------|------------------|
| Regular | Insulated | Regular | Insulated | |
| (Zinc Alloy) | | (Steel) | | |
| EMT Compression Fittings | | | | |
| CI5804 | CI5804-IT | CI5604 | CI5604-IT | 1/2 |
| CI5806 | CI5806-IT | CI5606 | CI5606-IT | 3/4 |
| CI5808 | CI5808-IT | CI5608 | CI5608-IT | 1 |
| CI5810 | CI5810-IT | CI5610 | CI5610-IT | 1-1/4 |
| CI5812 | CI5812-IT | CI5612 | CI5612-IT | 1-1/2 |
| CI5816 | CI5816-IT | CI5616 | CI5616-IT | 2 |
| CI5820 | CI5820-IT | CI5620 | CI5620-IT | 2-1/2 |
| CI5824 | CI5824-IT | CI5624 | CI5624-IT | 3 |
| CI5832 | CI5832-IT | CI5632 | CI5632-IT | 4 |

CI5904 / CI5932



CI5704 / CI5732



| Cat. No. | | Trade Size (in.) |
|----------------------------------|-----------|------------------|
| Regular | Insulated | |
| EMT Compression Couplings | | |
| CI5904 | CI5704 | 1/2 |
| CI5906 | CI5706 | 3/4 |
| CI5908 | CI5708 | 1 |
| CI5910 | CI5710 | 1-1/4 |
| CI5912 | CI5712 | 1-1/2 |
| CI5916 | CI5716 | 2 |
| CI5920 | CI5720 | 2-1/2 |
| CI5924 | CI5724 | 3 |
| CI5932 | CI5732 | 4 |

CI7538



| Cat. No. | Max. Flex. Conduit Dia. (in.) | Hole Size (in.) |
|---|-------------------------------|-----------------|
| One Hole Double Sided Strap (Galvanized Steel) | | |
| CI7538* * | 1.05 | 3/16 |

*Any combination of 3/8 in., 1/2 in. and 3/4 in. EMT, rigid conduit, flexible conduit or teck cables

Rigid Conduit

Accessories and Entrance Heads



CI1203 / CI1216



CI1503 / CI1548



| Cat. No. | Trade Size (in.) | Max. EMT Dia. (in.) | Hole Size (in.) |
|---|------------------|---------------------|-----------------|
| One Hole Rigid Straps (Galvanized Steel) | | | |
| CI1203 | 3/8 | 0.68 | 1/4 |
| CI1204 | 1/2 | 0.84 | 1/4 |
| CI1206 | 3/4 | 1.05 | 1/4 |
| CI1208 | 1 | 1.32 | 5/16 |
| CI1210 | 1-1/4 | 1.66 | 7/16 |
| CI1212 | 1-1/2 | 1.90 | 7/16 |
| CI1216 | 2 | 2.38 | 9/16 |
| Two Hole Rigid Straps (Galvanized Steel) | | | |
| CI1503 | 3/8 | 0.68 | 3/16 |
| CI1504 | 1/2 | 0.84 | 3/16 |
| CI1506 | 3/4 | 1.05 | 3/16 |
| CI1508 | 1 | 1.32 | 3/16 |
| CI1510 | 1-1/4 | 1.66 | 1/4 |
| CI1512 | 1-1/2 | 1.90 | 1/4 |
| CI1516 | 2 | 2.38 | 9/32 |
| CI1520 | 2-1/2 | 2.88 | 3/8 |
| CI1524 | 3 | 3.50 | 3/8 |
| CI1528 | 3-1/2 | 4.00 | 1/2 |
| CI1532 | 4 | 4.50 | 1/2 |
| CI1540 | 5 | 5.56 | 1/2 |
| CI1548 | 6 | 6.63 | 1/2 |

CIEFA-1/2 / CIEFA-4



| Cat. No. | Trade Size (in.) |
|---|------------------|
| Service Entrance Heads (Cast Aluminum) | |
| CIEFA-1/2 | 1/2 |
| CIEFA-3/4 | 3/4 |
| CIEFA-1 | 1 |
| CIEFA-1-1/4 | 1-1/4 |
| CIEFA-1-1/2 | 1-1/2 |
| CIEFA-2 | 2 |
| CIEFA-2-1/2 | 2-1/2 |
| CIEFA-3 | 3 |
| CIEFA-3-1/2 | 3-1/2 |
| CIEFA-4 | 4 |

Consult page D10 for technical specifications

CI7538



| Cat. No. | Max. Flex. Conduit Dia. (in.) | Hole Size (in.) |
|---|-------------------------------|-----------------|
| One Hole Double Sided Strap (Galvanized Steel) | | |
| CI7538* | 1.05 | 3/16 |

*Any combination of 3/8 in., 1/2 in. and 3/4 in. EMT, rigid conduit, flexible conduit or teck cables