## Raised Floor Systems

## Compresses #8 AWG through 4/0 AWG cable.

### **Signal Reference Grid Connector**

- Clamps onto pedestal posts up to 1" diameter square and 1¼" round
- · Can be used as an "X" or "T" configuration cable to post
- · High-conductivity wrought-copper construction



# INSTALLING TOOLS AND DIE CODES TBM14M AND TBM15I

CAT. NO.	CONDUCTOR	DIE CAT. NO.	DIE CODE	COLOR CODE
CDCO 4	#8	15527	29	GRAY
SRG8-4	#6 to #4	15528	33	BROWN
SRG2-1	#2 & #1	15508	42	PINK
SRG10-20	1/0 & 2/0	15530	50	ORANGE
SRG30-40	3/0 & 4/0	15511	54	PURPLE

### Secures signal reference grid wire to raised-floor support posts.

#### **Signal Reference Grid Clamp**

- Range-taking design accepts #8 to #4 AWG grid wire and fits 1" round and ¾" square trade size support posts
- · Lay-in feature means no kinks or bends
- Quick, easy installation
- Only one screw to tighten
- Enables grid wire to make direct, low-resistance contact with support posts
- Stamped-steel construction, zinc plated







CAT. NO.	DESCRIPTION	WIRE RANGE
3900	3/4" square to 1" round	#8–#4
3900BP (BULK PACK)	3/4" square to 1" round	#8-#4

UL File No. E-3060.

Approved for grounding and bonding per UL 467.

#### **Ground Electrode Boxes**

		WT. Stan		
CAT. NO.	DESCRIPTION	LB.	KG	PACKAGE
51628	Pregalvanized steel	1180	536.3	5
51629	Hot-dip galvanized	1200	545.4	5

14-gauge steel. 10" diameter, 12" depth.





**United States** 

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 **Technical Services** Tel: 888.862.3289

