



**2000i SDX 1RU/2RU/4RU RACK-MOUNT ENCLOSURES**

- Accepts SDX adapter plates, MTP® cassettes, splice trays, and splice modules
- Removable transparent hinged doors
- Sliding tray provides accessibility to front and rear of bulkhead after installation, and removes completely to facilitate field terminations and splicing
- 17-inch depth for high-density fiber termination and/or splicing
- Stackable and adjustable fiber rings simplify cable management
- Constructed of durable polycarbonate plastic and black powder-coated 16-gauge steel
- 19- or 23-inch rack-mount options (23-inch 1RU mounting bracket sold separately)
- 1RU and 2RU accept the HDX Retrofit Tray (sold separately) for higher density applications using HDX MTP Cassettes and Adapter Plates
- 1RU and 2RU enclosures are “intelligent ready,” accept Intact Fiber Upgrade Kits, see page F5



**RECOMMENDED APPLICATIONS:**

Data Centers

Equipment Room

Entrance Facility

Telecommunications Room

19" and 23" Racks and Cabinets

**2000i SDX RACK-MOUNT ENCLOSURES**

DESCRIPTION	MAXIMUM CAPACITY					PART NO.	
	FIBERS (USING LC)	ADAPTER PLATES	AND	SPLICE TRAYS/ MODULES*	OR		MTP® CASSETTES
<b>[A]</b> 1RU 2000i SDX Enclosure, empty, sliding tray	72	3		3		3	5R1UH-S03
<b>[B]</b> 2RU 2000i SDX Enclosure, empty, sliding tray	144	6		6		6	5R2UH-S06
<b>[C]</b> 4RU 2000i SDX Enclosure, empty, sliding tray	288	12		12		12	5R4UH-S12
<b>[D]</b> SDX Adapter Plates and Cassettes							See pages B25-B27.

\* = Maximum splice tray capacity is limited by height of selected splice tray.

**Make-to-Order! 2000i SDX RACK-MOUNT ENCLOSURE OPTIONS**

ENCLOSURE STYLE	ADAPTER PLATES OR MTP CASSETTE SELECTION	ADAPTER PLATE QTY	FIBER TYPE	ADAPTER TYPE & PIGTAIL SELECTION	SPLICE TRAY STYLE	NO. OF SPLICE TRAYS	SECURITY OPTIONS	CABLE CLAMP KIT	MOUNTING EAR POSITION
• 1U • 2U • 4U	<ul style="list-style-type: none"> <li>• 6 fibers (SC, ST)</li> <li>• 8 fibers (SC, ST)</li> <li>• 12 fibers (LC, SC, ST)</li> <li>• 16 fibers (LC only)</li> <li>• 24 fibers (LC only)</li> <li>• MTP Cassette - 12 fibers (LC, SC, ST)</li> <li>• MTP Cassette - 24 fibers (LC only)</li> </ul>	• 1-12	<ul style="list-style-type: none"> <li>• OM1</li> <li>• OM2</li> <li>• OM3</li> <li>• OM4</li> <li>• OM4+</li> <li>• OS2</li> </ul>	<ul style="list-style-type: none"> <li>• LC</li> <li>• LC + pigtail</li> <li>• SC</li> <li>• SC/APC</li> <li>• SC + pigtail</li> <li>• SC/APC + pigtail</li> <li>• ST</li> <li>• ST + pigtail</li> <li>• LC (Violet)</li> </ul>	<ul style="list-style-type: none"> <li>• Heat shrink, foam holders, up to 12 fibers (molded tray)</li> <li>• Heat shrink, plastic holders, up to 12 fibers (molded tray)</li> <li>• Bare fusion, plastic holders, up to 12 fibers (metal tray)</li> <li>• Heat shrink, plastic holders, up to 24 fibers (molded tray)</li> <li>• None</li> </ul>	<ul style="list-style-type: none"> <li>• 1-12</li> <li>• None</li> </ul>	<ul style="list-style-type: none"> <li>• Locking front door</li> <li>• Locking rear door</li> <li>• Both doors</li> <li>• None</li> </ul>	<ul style="list-style-type: none"> <li>• Yes</li> <li>• No</li> </ul>	<ul style="list-style-type: none"> <li>• 19"</li> <li>• 23"</li> </ul>

LightSpace® (LGX® footprint) compatible versions also available by special order.

For assistance customizing your enclosures, please visit [leviton.com/configurator](http://leviton.com/configurator) or call Tech Support at (800) 824 3005.