
15A, 20A | Plugs/Connectors, Flanged Inlets/Outlets

Residential Grade Plugs and Connectors, Flanged Inlets and Outlets

Leviton offers a large selection of 15 and 20 Amp residential grade straight blade plugs and connectors, available in a wide variety of features. These rugged performers are moisture, chemical and abuse resistant. Our EPTR rubber-backed plugs and connectors stand up to rough use, protecting against dirt and moisture. The deep-slotted, backed-out terminal screws draw backwire clamps securely over stripped leads for maximum conductivity.



Features and Benefits

- Triple-drive head screws standard, Phillips, Robertson
- NEMA configuration number and rating molded on face of device for easy identification
- Rubber body is dirt and moisture resistant
- Deep-slotted, backed out terminal screws draw backwire clamps securely for maximum conductivity
- Husk and module keyed for easy alignment during wiring
- Built-in cord grip adjusts automatically for use with #18-3 through #12-3 cords (.245"-.655")
- Motor base inlet accepts #10 max. copper or copper clad wire

PVC Plugs & Connectors

- Rugged PVC body resists moisture and chemicals
- Unique dimpled body design provides a secure grip
- Speed-thread assembly screws tighten with just a few quick turns

Armored Plugs & Connectors

- Ideal for shops, garages and rough-duty work with hard floors
- Two piece strain-relief clamp center cord for neat installation

Rubber-Back Plugs & Connectors

- Designed to stand up to rough use
- No internal metal parts exposed
- Elastomeric husk provides added protection against dirt and moisture entry into the back wire port
- Designed to operate in the widest possible temperature range



Straight Blade Devices

15A, 20A | Plugs/Connectors, Flanged Inlets/Outlets

Straight Blade Devices



101



102-WP



115PR

Easy Wire Plugs 🖲 🖲					
Rating		15A-125V			
NEMA		1-15P Polarized	(1) 1-15P		
Description	Color	Cat. No. Polarized	Cat. No. Non-Polarized	Wire Gauge (stranded)	
15A Non-Polarized Plug	White	_	321-W	#16/2 HPN, 15A (1875W)	
104 DI	Brown	-	321	#18/2 HPN, 1	
10A Plug	White	123-PW 123-PI	123-W	#18/2 SPT-1, 10A (1250W) #20/2XT, 3A (375W)	
	lvory Brown	123-PI 123-P	123-I 123		
2-Pole, 2-Wire Plugs 🗐	BIOWIT	101	180		
Rating		15A-125V			
NEMA		\frown	\bigcirc		
		1-15P Polarized	-		
Description	Color	Cat. No.	Cat. No.	Wire Gauge	Cord Dia.
		Polarized	Non-Polarized	(stranded)	(Inches)
Polarized Light Duty	White	101-WP	—	#20, 18, 16	Flat or Rounded
Clamptite Plug	Black	101-EP	_		up to .250
	Brown	101-P	_	007.1.007.0	
Non-Polarized Easy	White	_	101AN-W	SPT-1, SPT-2	Up to .250
Wire Angle Plug	Black	_	101AN-E		
Nee Delevized Leaver Duty	Brown	_	101AN	AVA/C 10 2 to	
Non-Polarized Heavy-Duty PVC Plug	Yellow	_	115PV	AWG 18-2 to 12-2 Cable	.245655
Non-Polarized Heavy-Duty	Black	_	115PR	AWG 18-2 to	.245655
TPE Rubber Plug	Dideit		110/10	12-2 Cable	.2 13 .000
Non-Polarized Short	White	_	48643-W	18-14	.375 max
Flat Vinyl Plug**	Black	_	48643-E		
, ,	Brown	_	48643		
Non-Polarized Vinyl Handle	Black	_	48646	18-14	.437 max
Plug with cord clamp**					
Non-Polarized Round Vinyl	Black	_	48642-E	18-14	.375 max
Handle Plug with Spring Blades					
2-Pole, 2-Wire Connectors	; (l) E				
Rating		15A-125V			
NEMA		1-15R Polarized			
Description	Color	Cat. No.	Cat. No.	Wire Gauge	Cord Dia.
		Polarized	Non-Polarized	(stranded)	(Inches)
Polarized Light Duty	White	102-WP	_	#20, 18, 16	Flat or Rounded
Clamptite Connector	Black	102-EP	_	.,,	up to .250
	Brown	102-P	_		1

*Not UL Listed. For replacement use only. CSA Certified except where indicated by **

with Cord Clamp**

Non-Polarized Vinyl Connector

Black

_

18-14

.437 max

612*



15A, 20A | Plugs/Connectors, Flanged Inlets/Outlets

15A 2-Pole, 3-Wire, Grounding — Residential 🖲 🚳							
Rating		15A-125V	15A-125V	15A-250V	15A-250V		
NEMA		5-15P	5-15R	6-15P	0-15R		
Description	Color	Cat. No. Plug	Cat. No. Connector	Cat. No. Plug	Cat. No. Connector	Wire Gauge (stranded)	Cord Dia. (Inches)
PVC Grounding	Yellow, Black or Orange	515PV	515CV	615PV (Yellow only)	_	AWG 18-12	.245655
Armored Grounding	Yellow/ Steel Armor	515PA	515CA	615PA	615CA	AWG 18-12	.245655
Rubber Grounding	Black	515PR	515CR	—	—	AWG 18-12	.245655
PVC Angle	White	515AN	_	—	-	AWG 18-12	.245655
20A 2-Pole, 3-Wir	e, Grounding	(D) (B .					
Rating		20A-125V	20A-125V	20A-250V	20A-250V		
NEMA							
		5-20P	5-20R	6-20P	6-20R		
Description	Color	Cat. No. Plug	Cat. No. Connector	Cat. No. Plug	Cat. No. Connector	Wire Gauge (stranded)	Cord Dia. (Inches)
PVC Grounding	Yellow	520PV	520CV	620PV	620CV	AWG 18-12	.2450655
Armored Grounding	Yellow/ Steel Armor	520PA	520CA	620PA	620CA	AWG 18-12	.2450655









15A 2-Pole, 3-Wire, Grounding — Commercial 🖲 🚱								
		15A-125V Inlet	Outlet	15A-250V Inlet	Outlet	Wire Gauge (stranded)		
Motor Base Inlet	Black	5239	_	5240	—	AWG 18-12	—	



5239

M