

LINEAR FLUORESCENT | Medium Bi-Pin Lamp

Medium Bi-Pin Linear Fluorescent T8 Lampholders

Features and Benefits

- Four-position lamp-lock socket rotates 90° forward and back, for quick relamping
- Lamp-lock models have slim, low profile silhouette that fits 22- to 25- gauge panels
- Chemical-resistant white thermoplastic body

Turn-Type 🖫 🚱		
Description	Rating	Cat. No.
Low Profile, Slide-On, with Captive Nut	660W 600V	13353-N
Tall Profile, Slide-On, with Captive Nut	660W 600V	13357-N
Tall Profile without Side Grooves, Slide-On, with Captive Nut	660W 600V	13359-N
Low Profile Disconnect, Slide-On	660W 600V	13351-D
Tall Profile Disconnect, Slide-On	660W 600V	13354-D
Low-Profile, Shunted, Slide-On	660W 600V	23351
Low-Profile, Slide-On	660W 600V	13351



13357-N

Straight-In ᠾ 🚱		
Description	Rating	Cat. No.
Low Profile, Slide-On	660W 600V	13150-UR5
Self-Locking, Slide-In, with Captive Nut. For use with T-8 Lamps	660W 600V	13451-N



13451-N

Snap-In/Slide-On Design and Lamp-Lock 🕦 🖫		
Description	Rating	Cat. No.
Snap-In or Slide-On Mounting Featuring Lamp-Lock,	660W 600V	13653-WP
with Panel Locator Post. For T-8 Lamps		
Same as Above, Less Locator Post	660W 600V	13653-NP
Same as 13653-WP, Except with Internal Shunt	660W 600V	23653-WP
Connection for Electronic Ballasts		
Same as Above, Less Locator Post	660W 600V	23653-NP
Snap-In or Slide-On Mounting Featuring Lamp-Lock, Optional	660W 600V	13652-WP
Panel Locator Post. For Energy-Efficient T-8 Lamps Only		
Same as 13652, Except with Internal Shunt.	660W 600V	23652-WP
Connection for Electronic Ballasts		
Snap-In or Slide-On Mounting Featuring Lamp-Lock, for	600W 600V	13652-WWP
Energy-Efficient T-8 Lamps Only. Wide-Wing Design		
Same as Above, Less Locator Post	600W 600V	13652-WNP
Same as 13652-WWP, Except with	600W 600V	23652-WWP
Internal Shunt Connection for Electronic Ballasts		
Same as Above, Less Locator Post	600W 600V	23652-WNP
Snap-In or Slide-On Mounting Featuring Lamp-Lock,	600W 600V	13653-WWP
for T-8 Lamps. Wide-Wing Design		
Same as Above, Less Locator Post	600W 600V	13653-WNP
Same as 13653-WWP, Except with	600W 600V	23653-WWP
Internal Shunt Connection for Electronic Ballasts		
Same as Above, Less Locator Post	600W 600V	23653-WNP



13351-D



13653-WP