

Couplings and Accessories

Stainless Steel Pipe Straps



Thomas & Betts offers stainless steel pipe straps to support and securely fasten rigid, IMC and EMT conduit. One- and two-hole stainless steel straps are ideal for industrial applications such as petro-chemical plants, manufacturing plants, pulp and paper mills, food processing, power plants, refineries and mining operations. Stainless steel pipe straps are also useful in commercial applications in schools, hospitals, office buildings, airports, casinos and stadiums.


- Higher degree of corrosion resistance than traditional zinc-plated or hot-dipped galvanized straps
- One and two-hole straps for EMT sizes ½" through 2"
- One and two-hole straps for Rigid and IMC size ½" through 4"
- 303 stainless steel

CAT. NO.	TRADE SIZE	WT. PER 100	HOLE DIA.	STD. PKG.	CAT. NO.	TRADE SIZE	WT. PER 100	HOLE DIA.	STD. PKG.
One-Hole EMT Straps					Two-Hole EMT Straps				
TS101-SS	½"	2.21	¼"	25	TS901-SS	½"	2.21	¼"	25
TS102-SS	¾"	2.49	¼"	25	TS902-SS	¾"	3.31	¼"	25
TS103-SS	1"	3.31	¼"	25	TS903-SS	1"	3.87	¼"	25
TS104-SS	1¼"	3.64	1/16"	10	TS904-SS	1"	7.54	1/16"	10
TS105-SS	1½"	3.87	1/16"	5	TS905-SS	1½"	12.21	1/16"	5
TS106-SS	2"	4.03	1/16"	5	TS906-SS	2"	18.23	1/16"	5
One-Hole Rigid/IMC Straps					Two-Hole Rigid/IMC Straps				
HS100-SS	¾"	2.00	9/32"	20	HS901-SS	½"	2.49	9/32"	20
HS101-SS	½"	2.21	9/32"	20	HS902-SS	¾"	3.64	9/32"	20
HS102-SS	¾"	2.49	9/32"	20	HS903-SS	1"	4.15	9/32"	20
HS103-SS	1"	3.48	9/32"	20	HS904-SS	1¼"	8.17	1/16"	10
HS104-SS	1¼"	3.76	1/32"	10	HS905-SS	1½"	17.50	1/32"	10
HS105-SS	1½"	18.22	1/32"	10	HS906-SS	2"	21.37	1/32"	5
HS106-SS	2"	19.69	1/32"	5	HS907-SS	2½"	21.54	1/32"	5
HS107-SS	2½"	67.21	1/32"	5	HS908-SS	3"	25.72	1/32"	5
HS108-SS	3"	76.45	1/32"	5	HS909-SS	3½"	27.27	1/32"	5
HS110-SS	4"	80.18	1/32"	5	HS910-SS	4"	31.70	1/32"	5

Conduit & Fittings — T&B® Rigid Fittings

Reduces threaded opening in conduit bodies or any female threaded fitting!

Threaded Reducers



- Smooth, built-in bushing completely covers rough ends of conduit
- Malleable iron or steel construction (steel through 606, also 614 and 615)


CAT. NO.		DIMENSION (IN.)	
STL. OR MI	ALUM.	SIZE	A
600TB	600ALTB	½" to ¾"	9/16"
601TB	601ALTB	¾" to 1"	9/16"
602TB	602ALTB	1" to 1½"	5/8"
603TB	603ALTB	1" to ¾"	5/8"
604TB	604ALTB	1¼" to 1½"	13/16"
605TB	605AL	1¼" to ¾"	5/8"
606TB	606AL	1¼" to 1"	15/16"
607	607AL	1½" to 1"	13/16"
608	608AL	1½" to ¾"	13/16"
609	609AL	1½" to 1"	15/16"
610	610AL	1½" to 1¼"	¾"
611TB	611AL	2" to 1½"	15/16"
612	612AL	2" to ¾"	15/16"
613	613AL	2" to 1"	15/16"
614TB	614AL	2" to 1¼"	15/16"
615TB	615AL	2" to 1½"	7/8"

UL File No. E-23018

CSA File No. 2884

Reduce knockout hole in outlet box!

Reducing Washers



- Used in pairs
- Interlock to form a rib that centers washers and conduit in knockout
- Galvanized steel construction

CAT. NO.	SIZE	DIMENSIONS (IN.)	
		A	B
3700	¾" to ¾"	1½"	45/64"
3701	¾" to ½"	1½"	7/8"
3702	1" to ¾"	1½"	45/64"
3703	1" to ½"	1½"	7/8"
3704	1" to ¾"	1½"	13/32"
3705-TB	1¼" to ¾"	2"	45/64"
3706	1¼" to ½"	2"	7/8"
3707	1¼" to ¾"	2"	13/32"
3708	1¼" to 1"	2"	123/64"
3709	1½" to ¾"	2¼"	45/64"
3710	1½" to ½"	2¼"	7/8"
3711	1½" to ¾"	2¼"	13/32"
3712	1½" to 1"	2¼"	123/64"
3713	1½" to 1¼"	2¼"	123/32"
3714	2" to ½"	2¾"	7/8"
3715-TB	2" to ¾"	2¾"	13/32"
3716	2" to 1"	2¾"	123/64"
3717	2" to 1¼"	2¾"	123/32"
3718	2" to 1½"	2¾"	133/32"

UL File No. E-13938

CSA File No. 2884