

Molded Case Circuit Breakers

QJ 225A Frame

Selection

Type QJ2[®]

Continuous Current Rating @ 40°C	2-Pole		3-Pole	
	240V AC		240V AC	
	Catalog Number	List Price \$	Catalog Number	List Price \$
60	QJ22B060■		QJ23B060	
70	QJ22B070■		QJ23B070	
80	QJ22B080■		QJ23B080■	
90	QJ22B090■		QJ23B090■	
100	QJ22B100		QJ23B100	
110	QJ22B110■		QJ23B110	
125	QJ22B125		QJ23B125	
150	QJ22B150		QJ23B150	
175	QJ22B175		QJ23B175	
200	QJ22B200		QJ23B200	
225	QJ22B225		QJ23B225	

Type QJH2[®]

60	QJH22B060■		QJH23B060■	
70	QJH22B070■		QJH23B070■	
80	QJH22B080■		QJH23B080■	
90	QJH22B090■		QJH23B090■	
100	QJH22B100■		QJH23B100	
110	QJH22B110■		QJH23B110	
125	QJH22B125		QJH23B125	
150	QJH22B150		QJH23B150	
175	QJH22B175■		QJH23B175	
200	QJH22B200		QJH23B200	
225	QJH22B225		QJH23B225	

Type QJ2H[®]

60	QJ22B060H■		QJ23B060H■	
70	QJ22B070H■		QJ23B070H■	
80	QJ22B080H■		QJ23B080H■	
90	QJ22B090H■		QJ23B090H■	
100	QJ22B100H■		QJ23B100H■	
110	QJ22B110H■		QJ23B110H■	
125	QJ22B125H		QJ23B125H	
150	QJ22B150H		QJ23B150H	
175	QJ22B175H■		QJ23B175H	
200	QJ22B200H		QJ23B200H	
225	QJ22B225H		QJ23B225H	

Type HQJ2H[®]

100	—	—	HQJ23B100H	▲
110	—	—	HQJ23B110H	▲
125	—	—	HQJ23B125H	▲
150	—	—	HQJ23B150H	
175	—	—	HQJ23B175H	▲
200	—	—	HQJ23B200H	
225	—	—	HQJ23B225H	▲

QJ2

Internal Accessories (Factory installed only) (3-pole only)^③
Add suffix to catalog number and adder to list price.

Control Voltage		Shunt Trip		Auxiliary Switches				Shunt Trip and 1A and 1B Auxiliary Switch	
AC	DC	Suffix	List Adder \$	1A and 1B		2A and 2B		Suffix	List Adder \$
				Suffix	List Adder \$	Suffix	List Adder \$		
120/240		00S01■		A01■		A02■		01S01■	
	24	00S07■		A01■		A02■		01S07■	
	125	00S11■		A01■		A02■		01S11■	

■ Built to order. Allow 2–3 weeks for delivery.

▲ Built to order. Allow 6–8 weeks for delivery.

① See Note: A page 17/67.

② HACR rated.

③ Internal accessories are not available on 2-pole QJ breakers.

Ordering Information

Load side TA1Q300 lugs are mounted and included when circuit breaker is ordered. For line and load lugs (TA1Q300) installed at no additional charge, add suffix "L" to catalog number.

50°C Calibration - See page 17/70.
400HZ. - See page 17/70.

Shipping Weights

QJ2, QJH2, QJ2H, HQJ2H		
Number of Poles	Number per Carton	Shipping Weight (lbs.)
2	10	30
3	10	41

Lugs For 75°C Wire^①

Catalog Number	Lug Body	Lug Wire Range
TA1Q300	Al	(1) #6–300 kcmil Cu (1) #4–300 kcmil Al
TC1Q250	Cu	(1) #6–250 kcmil Cu

Enclosures (Neutral Included)

Type	Catalog Number	List Price \$
1	EB3225(S)(F)	
3R (2-pole)	WB2225	
3R (3-pole)	WB3225	

UL 489 Interrupting Ratings

Breaker Type	AIR @ 240V AC
QJ2	10,000
QJH2	22,000
QJ2H	42,000
HQJ2H	100,000

