
PL17 Series


Polyphase 100 A 600 V Max.

Product Specifications

- Conductor range: 6-1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- · Primarily used in: All provinces




1-3/16 in.



OVERHEAD BOTTOM





COMBINATION AND UNDERGROUND BOTTOM



Cat. No.	Description	Dimensions (in.)			Weight Each	
		Н	W	D	lb.	kg
7 JAW						
PL17-INV	Overhead, hub opening	15-5/8	8-9/16	5-7/16	12	5.4
PL17-INV-HQ	Overhead, hub opening (Hydro-Quebec approved)					
PL17-INTV-HQ	Underground (Hydro-Quebec spec)					
PL17-INTCV	Combination overhead-underground					
PL17-INTCV-HQ	Combination overhead-underground (Hydro-Quebec approved)					
PL17-V	Overhead, hub opening					
PL17-TV	Underground					
PL17-TCV	Combination overhead-underground					
8 JAW						
PL17-8V	Overhead, hub opening	15-5/8	8-9/16	5-7/16	12	5.4
PL17-8TCV	Combination overhead-underground					
FACTORY INSTALLED ACCESSORIES						
Include: -IN	Insulated neutral					