
WALL PLATES & SPECIALTIES



SWP26LA

Screwless Polycarbonate Wall Plates

- A. Molded of rugged .065" thick polycarbonate.
- B. Seamless, sleek, super smooth construction provides no dirt-catching channel around plate's perimeter.
- C. Two-piece plastic subplate bridges recessed boxes and uneven sheet rock. Fixes floating installations.
- D. Automatic alignment pins ensure that devices are properly positioned so that wall plates fit perfectly.
- E. Oversized opening to accommodate all NEMA 26 decorator-style openings.
- F. An extra 1/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.



Specifications















Thermoset SP Series

Nylon TP Series

Screwless Polycarbonate SWP Series

302/304 Stainless Steel

Polished Brass

ed

Brushed Brass

Aluminum

Application

Legrand's broad line of Pass & Seymour® Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour devices.

Thermoset Plastic Wall Plates

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

Screwless Polycarbonate Wall Plates

- Molded of .065" thick polycarbonate, matte finish.
- 2-piece plastic subplate made of polycarbonate.
- Extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond; and three metallic finishes.


Metal Wall Plates

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel.
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302/304 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302/304, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates.
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.

Dimensions



Standard Size Wall Plates

- Standard size wall plates for all applications.
- Best fit for surface mount boxes.
- · Available in plastic and metal only.

Dimensions

1 gang 2.75" x 4.5" 2 gang 4.56" x 4.5" 3 gang 6.375" x 4.5" 4 gang 8.125" x 4.5" 5 gang 10" x 4.5" 6 gang 11.812" x 4.5" 13.62" x 4.5" 7 gang 15.44" x 4.5" 8 gang

TradeMaster® Wall Plates

- Extra 3/16" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and decorator single gang plates.

Dimensions

1 gang 2.9375" x 4.6875"
2 gang 4.75" x 4.6875"
3 gang 6.563" x 4.6875"
4 gang 8.375" x 4.6875"
5 gang 10.188" x 4.6875"
6 gang 12" x 4.6875"

Screwless Polycarbonate Wall Plates

- Available in decorator openings.
- Extra 1/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- 2-piece plastic subplate made of polycarbonate.
- Available in 3 metallic finishes and 6 standard colors.

Wall Plate Dimensions

1 gang 3.10" x 4.87" 2 gang 4.912" x 4.87" 3 gang 6.724" x 4.87" 4 gang 8.536" x 4.87"

Subplate Dimensions

1 gang 2.85" x 4.62" 2 gang 4.662" x 4.62" 3 gang 6.474" x 4.62" 4 gang 8.286" x 4.62"

Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates.
- Additional coverage for sheet rock gaps.
- Available in plastic and metal only.

Dimensions

1 gang 3.125" x 4.87" 2 gang 4.93" x 4.87" 3 gang 6.75" x 4.87" 4 gang 8.56" x 4.87"

TradeMaster® Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle, and decorator single gang plates.

Dimensions

1 gang 3.3125" x 5.0625" 2 gang 5.125" x 5.0625" 3 gang 6.9375" x 5.0625" 4 gang 8.75" x 5.0625"

Jumbo Wall Plates


- Extra 3/4" width and height than Standard size wall plates.
- Largest size wall plates to cover larger wall damage.
- Available in plastic and metal only.

Dimensions

1 gang 3.5" x 5.25" 2 gang 5.31" x 5.25" 3 gang 7.12" x 5.25" 4 gang 8.93" x 5.25"



Dimensions




Sectional Wall Plates

End and center panels with each of five most-used configurations make it possible to improvise custom wall plates on the job. Panels lock securely together on installation. Blank sections furnished with mounting strap.


Wall Plate Mountings

Illustrated are the five standard methods of plate mounting. There are many other non-standard methods which depend upon the special device used. Exact mounting hole specifications for every device appear in the Selector Guide.





Wall Plate Sizes

Standard Size




TradeMaster® Size Available in nylon only







TradeMaster Jumbo Available in nylon only



Jumbo




Tandem Wall Plates



Metal only. Plate mounting dimensions are non-standard. Refer to Page P-26 for details and devices that can be used.

Screwless Wall Plate Plastic Subplate



For Screwless (SWP) Wall Plate dimensions refer to Page P-4.



Decorator Openings & Blank Plates Junior-Jumbo & Jumbo Plastic & Metal


		NYLON	THERMOSET		METAL		
		TRADEMASTER®	JUNIOR-JUMBO	JUMB0		JUNIOR-JUMBO	JUMB0
DESCRIPTION	COLOR	JUMB0	SMOOTH	SM00TH	MATERIAL	SMOOTH	SM00TH
DECORATOR OPENINGS							
One Gang	lvory White Brown Gray Red	TPJ26I TPJ26W TPJ26 TPJ26GRY TPJ26RED	SPJ26I SPJ26W SPJ26	SP026I SP026W SP026	Brass 302/304 S/S	SBJ26 SSJ26	SB026 SS026
Two Gang	Light Almond Ivory White Brown Gray Light Almond	TPJ26LA TPJ262I TPJ262W TPJ262 TPJ262GRY TPJ262LA	SPJ26LA SPJ262I SPJ262W SPJ262	SP026LA SP0262I SP0262W SP0262	302/304 S/S	SSJ262	SS0262
Three Gang	Ivory White Brown Gray Light Almond	TPJ263I TPJ263W TPJ263 TPJ263GRY TPJ263LA	SPJ263 SPJ263W SPJ263		302/304 S/S	SSJ263	
Four Gang	Ivory White Brown Gray Light Almond	TPJ264I TPJ264W TPJ264 TPJ264GRY TPJ264LA	SPJ264I SPJ264W SPJ264 SPJ264LA				
BLANK PLATES - E							
One Gang Blank Box Mtd.	Ivory White Brown Gray Light Almond	TPJ13I TPJ13W TPJ13 TPJ13GRY TPJ13LA	SPJ13I SPJ13W SPJ13	SP013I SP013W SP013	302/304 S/S	SSJ13	SS013
Two Gang Blank Box Mtd.	lvory White Brown			SP023I SP023W SP023	302/304 S/S		SS023
Three Gang Blank Box Mtd.					302/304 S/S		SS033
One Gang Strap Mtd.					302/304 S/S		SS014
Two Gang Blank Strap Mtd.					302/304 S/S		SS024
Three Gang Blank Strap Mtd.					302/304 S/S		SS034


These products listed to UL514, Cover Plates for Flush-Mounted Wiring Devices, CSA Certified.


Custom Metal Wall Plates Special Configurations

Chart B: Paint Finish Selection

These charts are for Custom Metal Wall Plates ONLY. For Devices & Wall Plates Color Selection Charts, see Pages A-29, B-87 and P-58.







Only available on Stainless Steel and Aluminum Plate Material. Colors may vary slightly. All Paint Finishes are gloss, except primer and flat black.

Chart C: Metal Finish Selection



Bright Chromium US #26 СН



Brushed Copper ВС



Brushed Bronze US #10 ΒZ



Brushed Brass Standard Finish ВВ

For additional colors consult factory.

FINISH SUFFIX PB*

^{*}Order with Brass Plate Material Prefix Only.