

## SLATER® PLASTIC BOXES

## Tamper-Resistant Floor Box Assemblies For Wood Sub-Floors



FB1TRSRB



FB1TRDRB

## Features – FB Series

- Tamper-resistant receptacles feature dual mechanical shutter system to help prevent insertion of foreign objects.
- Meets NEC 406.11 requirements.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.

CATALOG NUMBER	CU. IN. VOL.	DESCRIPTION	COVER PLATE FINISH	DIMENSIONS (IN.)			QTY. PER CARTON
				L	W	D	
<b>FLOOR BOX ASSEMBLIES — ONE GANG FOR WOOD SUB-FLOORS</b>							
<b>FB1TRSRB</b> <b>FB1TRSRN</b>	20.5	Single threaded screw plug. Includes 15A, 125V single tamper-resistant receptacle.	Brass Nickel	4¾	3¾	4	1
<b>FB1TRDRB</b> <b>FB1TRDRN</b>	20.5	#8 duplex opening, 2 threaded screw plugs. Includes 3232 tamper-resistant 15A, 125V duplex receptacle.	Brass Nickel	4¾	3¾	4	1

**National Electrical Code® Section 406.11 Tamper-Resistant Receptacles in Dwelling Units.**

In all areas specified in 210.52 all 125-volt, 15- and 20-amp receptacles shall be listed tamper-resistant receptacles.