

Super-Tack Polyester Component Labels

- Provide durability; high-temperature resistance and dimensional stability; does not stretch or easily tear; and has high-tack permanent adhesive
- Used to identify patch panels, faceplates, punchdown blocks, and other network systems hardware
- Use thermal transfer resin ribbon
- Temperature range: -40°F to 302°F (-40°C to 150°C)
- UL969 recognized, File # MH14979; cUL recognized, C22.2 No. 0.15.01, File # MH14979



Part Number	Color	Width		Height		Type of Application	Labels Per Row	Std. Pkg. Qty.
		In.	mm	In.	mm			
C061X030YPT	White	0.61	15.5	0.30	7.6	1-port	4	2500
C100X050YPT	White	1.00	25.4	0.50	12.7	general identifier	3	10000
C125X030YPT	White	1.25	31.8	0.30	7.6	2-port	3	2500
C138X019YPT	White	1.38	35.1	0.19	4.8	module	1	2500
C138X019Y0T	Black	1.38	35.1	0.19	4.8	module	1	2500
C188X030YPT	White	1.88	47.8	0.30	7.6	3-port	1	2500
C200X100YPT	White	2.00	50.8	1.00	25.4	general identifier	1	2500
C200X100Y0T	Black	2.00	50.8	1.00	25.4	general identifier	1	2500
C252X030YPT	White	2.52	64.0	0.30	7.6	4-port	1	2500
C252X030YPT-P*	White	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YQT-P*	TIA Blue	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YRT-P*	TIA Brown	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YST-P*	TIA Green	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YTT-P*	TIA Gray	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YUT-P*	TIA Orange	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YVT-P*	TIA Purple	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030YWT-P*	TIA Red	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030Y0T-P*	Black	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030Y8T-P*	TIA Yellow	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C252X030Y9T-P*	Gold	2.52	64.0	0.30	7.6	1, 2, 3 or 4-port	1	2500
C261X030YPT	White	2.61	66.3	0.30	7.6	4-port	1	2500
C275X125YPT	White	2.75	69.9	1.25	31.8	general identifier	1	2500
C275X125Y0T	Black	2.75	69.9	1.25	31.8	general identifier	1	2500
C288X030YPT	White	2.88	73.2	0.30	7.6	5-port	1	2500
C300X200YPT	White	3.00	76.2	2.00	50.8	general identifier	1	2500
C315X030YPT	White	3.15	80.0	0.30	7.6	5-port	1	2500
C379X030YPT	White	3.79	96.3	0.30	7.6	6-port	1	2500
C379X030YPT-P*	White	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YQT-P*	TIA Blue	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YRT-P*	TIA Brown	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YST-P*	TIA Green	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YTT-P*	TIA Gray	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YUT-P*	TIA Orange	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YVT-P*	TIA Purple	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030YWT-P*	TIA Red	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030Y0T-P*	Black	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030Y8T-P*	TIA Yellow	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C379X030Y9T-P*	Gold	3.79	96.3	0.30	7.6	1, 2, 3, 4, 5 or 6-port	1	2500
C400X200Y8T	Yellow	4.00	101.6	2.00	50.8	general identifier	1	1000
C400X300YPT	White	4.00	101.6	3.00	76.2	general identifier	1	2500

*Label is perforated to be used in 1, 2, 3, 4, or 6-Port position applications.
 Order number of labels required in multiples of Standard Package Quantity.
 Labels are roll mounted on 3.00" cores; when using the TDP43ME printer and 3.00" cores, the roll stand (TDP43ME-RS) is required.