





Wedge Base Lampholders

Wedge base lampholders are an economical choice for linear lighting applications. They have a minimal profile and produce bright, uniform illumination. They are compatible with wedge base lamps that are 10W or less and T3-1/4 size or smaller including xenon, LED, etc. Xenon lamps emit a white light that approximates the color of halogen, but have up to a 20,000-hour lamp life and do not require fixture lenses or special handling.



	Catalog #	Finish	Lamp	Dimensions
	TL201WH TL201BL	White Black	One 12V or 24V, 10W max. T3-1/4 wedge base lamp	 5/8" 1 3/8"
	Catalog #	Finish	Lamp	Dimensions
	TL202WH TL202BL	White Black	Two 12V or 24V, 10W max. T3-1/4 wedge base lamps	 5/8" 2 3/8"

T3-1/4 Xenon Wedge Base Lamps

Catalog #	Watts	Volts	Clear/Frosted	Rated Lumens	Catalog #	Watts	Volts	Clear/Frosted	Rated Lumens
TL900	3	12	Clear	15	TL905-24V	5	24	Frosted	29
TL901	5	12	Clear	33	TL910-24V	10	24	Frosted	91
TL903	10	12	Clear	83					

Rigid Loop Lampholder

Rigid loop lampholders are ideally suited for linear lighting applications. They have a low profile and produce bright, uniform illumination. The rigid loop lampholder includes a stationary reflector to forward project more of the 360° light from the lamp. They are compatible with rigid loop style lamps that are 10W or less and T3-1/4 size or smaller including xenon, LED, etc. Rigid loop lamps possess all of the advantages of the wedge base lamps, but offer a more symmetrical light distribution and slightly higher output that is optimal for cove lighting applications. Xenon lamps emit a white light that approximates the color of halogen, but have up to a 20,000-hour lamp life and do not require fixture lenses or special handling.



	Catalog #	Finish	Lamp	Dimensions
	TL211WH TL211BL	White Black	One 12V or 24V, 10W max. T3-1/4 rigid loop lamp	 1 1/16" 2 1/8"

T3-1/4 Xenon Rigid Loop Lamps

Catalog #	Watts	Volts	Clear/Frosted	Rated Lumens	Catalog #	Watts	Volts	Clear/Frosted	Rated Lumens
TL950CL	5	12	Clear	45	TL952CL-24V	5	24	Clear	40
TL950FR	5	12	Frosted	45	TL952FR-24V	5	24	Frosted	40
TL951CL	10	12	Clear	100	TL953CL-24V	10	24	Clear	90
TL951FR	10	12	Frosted	100	TL953FR-24V	10	24	Frosted	90

Festoon Lampholder

Festoon lampholders are ideally suited for linear lighting applications. They have a low profile and produce bright, uniform illumination. The festoon lampholder includes an articulating reflector, enabling more precise aiming of the light. They are compatible with festoon type lamps that are 10W or less and T3-1/4 size or smaller including xenon, LED, etc. The festoon lamp is similar to the rigid loop lamp, though more widely available and offering slightly greater light output. Xenon lamps emit a white light that approximates the color of halogen, but have up to a 20,000-hour lamp life and do not require fixture lenses or special handling.

	Catalog #	Finish	Lamp	Dimensions
	TL212WH TL212BL	White Black	One 12V or 24V, 10W max. T3-1/4 festoon lamp	 1" 3/4" 2"

Xenon T3-1/4 Festoon Lamps

Catalog #	Watts	Volts	Clear/Frosted	Rated Lumens	Catalog #	Watts	Volts	Clear/Frosted	Rated Lumens
TL960CL	5	12	Clear	50	TL964CL-24V	5	24	Clear	50
TL960FR	5	12	Frosted	50	TL964FR-24V	5	24	Frosted	50
TL961CL	10	12	Clear	120	TL965CL-24V	10	24	Clear	120
TL961FR	10	12	Frosted	120	TL965FR-24V	10	24	Frosted	120