

### Lampholder adapters & accessories

#### Product description

Keyless switch  
Medium base  
660W, 250V/AC

#### Design features

- One piece screwshell with porcelain base

#### Socket extensions



Rating		Description	Color	Catalog no.	
W	V/AC				
660	250	Phenolic medium base socket, extends 1.38" (34.9mm)	BK	□ 1054	•

Listed to UL496, file no. E15055; CSA certified to C22.2, no. 43; NOM certified



1054

### Lampholder adapters & accessories

#### Product description

Lamp guards

#### Design features

- 1.50" (38.1mm) clamp fits ceiling lampholders, sign and scoreboard Attachon lampholders
- 1465 is high-strength impact-resistant thermoplastic
- Easy-open guard permits relamping without removing guard

#### Lamp guards

Description	Color	Catalog no.	
Metal lamp guard with 1.50" (38.1mm) collar, 100W bulb max.	Steel	□ 469B	
Plastic lamp guard with adjustable collar, 200W max.	Y	□ 1465Y	•



469

#### Color ordering information:

BK (Black), Steel, Y (Yellow)



**Dimensional information:** B-73 **Specification information:** Please visit [www.eaton.com/wiringdevices](http://www.eaton.com/wiringdevices)  
**Compliances, specifications and availability are subject to change without notice.**

Indicates NAFTA compliant - Page G-21

RoHS compliant - Page G-21