

# Pushbutton Enclosures - NEMA 12, 13

**Miniature Pushbutton MPB Series** 














MPB2




MPB3




MPB4



MPB6



MPB9



**MPB12** 

## **Application**

- Designed to accept 22mm miniature oil tight pushbuttons, switches and pilot lights.
- · Provides protection from dirt, dust, oil and water.

### **Standards**

- UL 508 Type 12 and 13
- CSA Type 12 and 13
- · Complies with
  - NEMA Type 12 and 13
  - JIC EMP-1-1967
  - JIC EGP-1-1967
  - IEC 60529, IP54
- Appropriate components are required to maintain these standards.

#### Construction

- Formed 14 gauge steel except the MPB1 which is 16 gauge.
- Smooth continuously welded seams.
- · Welded brackets provide for enclosure mounting.
- · Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see table).
- · Oil resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

#### Finish

 Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

#### **Accessories**

- Hole plugs...see page 435
- Pedestals...see page 454

Technical references and CAD downloads available at www.hammondmfg.com


All dimensions in inches unless specified otherwise

Canada: 519.822.2960 or 905.456.3770




# Pushbutton Enclosures - NEMA 12, 13

Miniature Pushbutton MPB Series







Hinge Detail
Retractable pin allows door to be mounted on left or right side

Ø 0.88	<u></u>						
	0.50						
0.13							
22.5mm Detail							

	No. of						Overall Dimensions				Ship	
Part No.	Holes	Α	В	С	D	Е	F	G	L	W	Z	Wt. lbs.
MPB1 <sup>1</sup>	1	3.25	2.75	3.50	1.88	3.75	1.71	2.50	4.25	3.06	3.56	2
MPB2 <sup>1</sup>	2	5.13	2.75	3.50	1.88	5.63	1.71	4.38	6.13	3.06	5.44	3
MPB3 <sup>1</sup>	3	7.00	2.75	3.50	1.88	7.50	1.71	6.25	8.00	3.06	7.31	3
MPB4 <sup>1</sup>	4	8.88	2.75	3.50	1.88	9.38	1.71	8.13	9.88	3.06	9.19	4
MPB6	6	8.50	5.00	4.25	4.13	9.00	3.96	7.75	9.50	5.31	8.81	5
MPB9	9	8.50	6.50	4.25	5.63	9.00	5.46	7.75	9.50	6.81	8.81	6
MPB12	12	10.38	6.50	4.25	5.63	10.88	5.46	9.63	11.38	6.81	10.69	6

<sup>&</sup>lt;sup>1</sup> Not hinged

Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise

Data Subject to change without notice