

## Rack Accessories Panels

### 19" Filler Panels

- Install in unused rack space to improve both cooling efficiency and system esthetics.
- Rugged black powder paint finish.
- Smooth paint finish for easy labeling.
- Requires mounting hardware
- Other colors and sizes available

Part No.	Description
<b>PBPS19001BK2</b>	1U Solid Steel Panel
<b>PBPS19003BK2</b>	2U Solid Steel Panel
<b>PBPS19005BK2</b>	3U Solid Steel Panel

Part No.	Description
<b>PPFS19001BK2</b>	1U Steel Perforated Panel
<b>PPFS19003BK2</b>	2U Steel Perforated Panel
<b>PPFS19005BK2</b>	3U Steel Perforated Panel

Part No.	Description
<b>PBFS19001BK2</b>	1U Formed Solid Steel Panel
<b>PBFS19003BK2</b>	2U Formed Solid Steel Panel
<b>PBFS19005BK2</b>	3U Formed Solid Steel Panel

Part No.	Description
<b>PBPA19001BK2</b>	1U Aluminum Steel Panel
<b>PBPA19003BK2</b>	2U Aluminum Steel Panel
<b>PBPA19005BK2</b>	3U Aluminum Steel Panel

### PBPS Series

- Solid, flat steel panel
- 14 Gauge steel, More economical than aluminum (PBPA series)
- Standard rack mount punching on both ends

### PPFS Series

- Perforated steel panel
- Folded 16 ga. steel construction

### PBFS Series

- Solid, flat steel panel
- 16 Gauge steel
- Includes a 0.50" fold, top and bottom for added strength
- Standard rack mount punching on both ends

### PBPA Series

- Solid, flat aluminum panel
- 0.125" thick aluminum
- Available in more economical steel version (PBPS series)
- Unfinished version is white paper covered on one side to protect finish
- Standard rack mount punching on both ends

### Cable Management Panels

- Requires mounting hardware
- Rugged textured black powder paint finish



Part No.	Description
<b>PCMDD19001BK1</b>	1U Hinged Horizontal Cable Manager (2.5" Overall Depth)
<b>PCMDD19003BK1</b>	2U Hinged Horizontal Cable Manager (2.5" Overall Depth)
<b>PCMDD19005BK1</b>	3U Hinged Horizontal Cable Manager (2.5" Overall Depth)



Part No.	Description
<b>PCMBBS19001BK1</b>	1U Steel Ring Panel
<b>PCMBBS19003BK1</b>	2U Steel Ring Panel
<b>PCMBBS23001BK1</b>	1U Steel Ring Panel 23" Mounting
<b>PCMBBS23003BK1</b>	2U Steel Ring Panel 23" Mounting



Part No.	Description
<b>PCMDSS19001BK1</b>	1U Hinged Finger Panel
<b>PCMDSS19003BK1</b>	2U Hinged Finger Panel
<b>PCMDSS19005BK1</b>	3U Hinged Finger Panel

### Cable Manager Panel

- Continuous hinged door with magnetic closure strip
- Four oblong openings (3.5" x 1.56") top & bottom - allowing for cable exit top and/or bottom
- Openings in the rear for cable entry/exit
- Standard 19" rack panel mount
- Available in 3 panel heights
- 2.5" overall depth

### Ring Panel

- Five steel rings welded to a folded 19" rack panel
- Rings extend 3.5" from panel front

### Metal Finger Panel

- 19" rack mount
- Snap open, hinged door
- Rack mount side has five slotted openings
- Extends 3" (not including snap buttons) from rack rails

*Please note this is a very small sample of our available panels. We have panels ranging in rack unit size up-to 18U. Visit [www.hammondmfg.com](http://www.hammondmfg.com) for more details.*