

Nail Eater® Extreme Black Utility Auger Bits



- Teflon® coating resists heat and friction for fast and smooth operation.
- Patented cutting edge cuts nails and staples so the bits last longer over time.
- Over center flute design evacuates chips faster, no clogging or chip flyback.
- Less power required to drill holes – extending battery life by up to 30% .
- Made in the USA.

| CAT. NO. | UPC NO. | DESCRIPTION | QTY. |
|------------|---------|---|------|
| 66TF-9/16 | 02004 | IMPACT AUGER BIT, TF-9/16" x 18" (POP) | 1 |
| 66TF-11/16 | 02005 | IMPACT AUGER BIT, TF-11/16" x 18" (POP) | 1 |
| 66TF-13/16 | 02006 | IMPACT AUGER BIT, TF-13/16" x 18" (POP) | 1 |
| 66TF-15/16 | 02007 | IMPACT AUGER BIT,TF-15/16" x 18" (POP) | 1 |

SPECIFICATIONS

| | | |
|--------------|--|---------------------|
| 9/16 | 18" X 1.5" X 1.5" (47.52 cm X 3.81cm X 3.81cm) | 0.8 lbs (362.87 g) |
| 11/16 | 18" X 1.5" X 1.5" (47.52 cm X 3.81cm X 3.81cm) | 1.05 lbs (476.27 g) |
| 13/16 | 18" X 1.5" X 1.5" (47.52 cm X 3.81cm X 3.81cm) | 1.3 lbs (589.67 g) |
| 15/16 | 18" X 1.5" X 1.5" (47.52 cm X 3.81cm X 3.81cm) | 1.75 lbs (793.78 g) |

Stubby Auger Wood Bits



- Over center single flute design for cleaner holes and less splintering.
- Unique cutting edge design for fast and smooth cutting action.
- Shorter than the top competitor's bit for better access to tight spaces between studs and joists.
- Perfect for drilling 2" and 4" joists.
- Augers have self-feeding screw point that draws bit through all wood types with less operator fatigue.
- Eliminates the need for special tools such as expensive right angle drills or multiple steps to cut the hole to size.
- 1/4" hex quick change design for fast and easy use in all drill types.
- Clearly marked with bit diameter and catalog number on shank for easy identification.

| CAT. NO. | UPC NO. | HOLE DIA. DIAMETER | | OVERALL LENGTH | | WEIGHT | |
|----------|---------|--------------------|------|----------------|-----|--------|-----|
| | | INCH | MM | INCH | MM | LBS | G |
| 60A-5/8 | 12416 | 5/8 | 15.9 | 4.5 | 144 | 0.3 | 118 |
| 60A-3/4 | 12417 | 3/4 | 19.1 | 4.5 | 144 | 0.3 | 136 |
| 60A-7/8 | 12418 | 7/8 | 22.2 | 4.5 | 144 | 0.3 | 149 |
| 60A-1 | 10538 | 1 | 25.4 | 4.5 | 144 | 0.4 | 199 |

| CAT. NO. | UPC NO. | DESCRIPTION |
|----------|---------|----------------------------|
| 60A-5/8 | 12416 | 5/8" Stubby Auger Wood Bit |
| 60A-3/4 | 12417 | 3/4" Stubby Auger Wood Bit |
| 60A-7/8 | 12418 | 7/8" Stubby Auger Wood Bit |
| 60A-1 | 10538 | 1" Stubby Auger Wood Bit |

