

MagnumPRO™ Fiberglass Fish Tapes





- · Rugged case design improves drop impact capability.
- · Non-conductive fiberglass tape with patented low-friction coating for faster and easier fishing.
- · Perfect for fishing in conduit with wire or cable present.
- · Superior rapid tape pay-out and rewind.
- Improved low profile tip for easy fishing through all sizes of conduit.
- Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly.
- · Exclusive, unique, lightweight reel for easy positive feed out and rewind.

SPECIFICATIONS

Capacity	540 Series- 0.175" (4.4 mm) dia 300 lbs. (1.3 kN) maximum design strength 542 Series-3/16" (4.7 mm) dia 400 lbs. (1.7 kN) maximum design strength
Weight	FTF540-50 - 2.8 lbs. (1.3 kg) FTF540-100 - 3.4 lbs. (1.5 kg) 542-200- 16 lbs. (7.2 kg) 542-250- 17 lbs. (7.7 kg)

	0.12 200 11 120 (1.11.13)					
	CAT. NO.	UPC NO.	DESCRIPTION			
	FTF540-50	12717	Fiberglass Fish Tape - 50' \times 11/64" (15.2 m \times 4.3 mm)			
	FTF540-100	12718	Fiberglass Fish Tape - $100' \times 11/64''$ (30.5 m × 4.3 mm)			
	542-150	35745	Fiberglass Fish Tape 150' \times 3/16" (61 m \times 4.8 mm)			
			IN REEL STAND			
	542-200	35746	Fiberglass Fish Tape 200' × 3/16" (61 m × 4.8 mm) IN REEL STAND			
	542-250	35747	Fiberglass Fish Tape 250' \times 3/16" (76.2 m \times 4.8 mm)			
			IN REEL STAND			
R	R540-100	35744	Replacement Fiberglass Tape - 100' × 11/64" (NO CASE)			
R	05157	05157	Replacement Fiberglass Tape - 200' × 3/16" (NO CASE)			
R	05158	05158	Replacement Fiberglass Tape - 250' × 3/16" (NO CASE)			
R	10565	10565	Pulling Eye Repair Kit for 11/64" (4.3mm) Diameter Fish Tapes			
			(Includes: pulling eye & adhesive)			
R	35750	35750	Accessory Kit for 3/16" (4.78 mm) Fish Tapes (Includes flexible			
			pulling leader, flexible pushing leader, pulling eye, splice ferrule			
			and threaded ferrule)			
R	35908	35908	1/8" (3 mm) Repair Kit (Includes threaded end ferrule, splice fer-			
_			rule and pulling eye)			
R	35909	35909	3/16" (4.7 mm) Repair Kit (Includes threaded end ferrule, splice			
_			ferrule and pulling eye)			
Α	35919	35919	1/8" (3 mm) Pulling Eye			
A	35930	35930	3/16" (4.7 mm) Pulling Eye			

MagnumPRO™ Nylon Fish Tapes



- Non-conductive, curl resistant nylon tape for fast, clean fishing.
- Good for fishing in conduit with wire or cable present.
- Rugged case design improves drop impact capability.
- Advanced comfort handle grip reduces fatigue.
- Nylon fish tape is intended for fishing only. Rope or line is recommended for pulling.

SPECIFICATIONS

Capacity	3/16" (4.8 mm) diameter – 250 lbs. (1.1 kN) maximum design strength
Weight	FTN536-50 – 2.9 lbs. (1.3 kg)
	FTN536-100 - 3.6 lbs. (1.6 kg)

R	CAT. NO.	UPC NO.	DESCRIPTION
	FTN536-50	12715	Nylon Fish Tape 50' \times 3/16" (15.2 m \times 4.8 mm)
	FTN536-100	12716	Nylon Fish Tape $100' \times 3/16'' (30.5 \text{ m} \times 4.8 \text{ mm})$
	RN536-50	12483	Replacement Nylon Fish Tape 50' (NO CASE)
R	RN536-100	12484	Replacement Nylon Fish Tape 100' NO CASE)
R	01664	01664	Replacement Tip for 436 Nylong Fish Tape (Requires Greenlee
			K05 or K09 series crimper or #6 hex crimp to install.)