## MagnumPRO™ Nylon Fish Tapes



- Non-conductive, curl resistant nylon tape for fast, clean fishing.
- Good for fishing in conduit with wire or cable present.
- Rugged case design improves drop impact capability.
- Advanced comfort handle grip reduces fatigue.
- Nylon fish tape is intended for fishing only. Rope or line is recommended for pulling.

CAT. NO.	UPC NO.	DESCRIPTION
FTN536-50	12715	Nylon Fish Tape 50' $\times$ 3/16" (15.2 m $\times$ 4.8 mm)
FTN536-100	12716	Nylon Fish Tape $100' \times 3/16''$ (30.5 m × 4.8 mm)
RN536-50	12483	Replacement Nylon Fish Tape 50' (NO CASE)
RN536-100	12484	Replacement Nylon Fish Tape 100' NO CASE)
01664	01664	Replacement Tip for 436 Nylong Fish Tape (Requires Greenlee
		K05 or K09 series crimper or #6 hex crimp to install.)
10052	10052	12" Case/Handle Replacement Kit

## **SPECIFICATIONS**

Capacity	3/16" (4.8 mm) diameter – 250 lbs. (1.1 kN) maximum design strength			
Weight	FTN536-50 - 2.9 lbs. (1.3 kg)			
	FTN536-100 – 3.6 lbs. (1.6 kg)			

## Flex-O-Twist® Flexible Fish Tape Leader



- Helps guide 1/8" steel tapes through sharp bends.
- Thread on the end of the fish tape in place of the swivel ball head.

CAT. NO.	UPC NO.	DESCRIPTION			
439-1	30859	12" (305 mm) Flexible Fish Tape Leader			
SPECIFICATIONS					
Weight	1.31	bs. (0.6 kg)			

## **SpeedFlex® Flexible Fish Tape Leader**



- Silver-solder joint attaches to any 1/8" (3.2 mm) x .060" (1.5 mm) steel fish tape to provide a slim profile that fishes farther, faster.
- · High-strength stainless steel cable is used for reliability and long life.
- · Beveled edges on the leader reduce the possibility of hangups when pulling wire.
- Up to (6) #10 wires can be attached to the large pulling eye.

CAT. NO.	UPC NO.	DESCRIPTION			
439-2	14392	12" (305 mm) SPEED FLEX Leader (solder joint)			
SPECIFICATIONS					
SPECIFICA	TIONS				

