



FISH TAPES

MagnumPRO[™] Oil-Tempered Spring Steel Fish Tapes

NEW



- Oil-tempered spring steel for excellent fishing performance.
- Dirt-free tape finish keeps hands cleaner during use.
- Advanced comfort handle grip reduces fatigue.
- Superior rapid tape pay-out and rewind.
- Smaller Fish Eye with offset bend for improved fishing ability.
- Improved low profile tip for easy fishing through all sizes of conduit.
- Viewing Port gives visibility to remaining tape and ability to remove jobsite debris quickly.
- Rugged case design improves drop impact capability.
- Flared case with Grip Ridges for no slip handling.
- Available in 50' (15.2 m), 65' (19.8 m), 125' (38.1 m) and 240' (73.2 m) lengths.
- 1/8", 1/4" and flat steel profiles to accommodate different fishing situations.

CAT. NO.	UPC NO.	DESCRIPTION
438-5H	07500	Steel Fish Tape - 50' × 1/8" (15.2 m × 3.2 mm)
FTS438-65	12729	Steel Fish Tape - 65' × 1/8" (19.8 m × 3.2 mm)
FTS438-65BP	10028	Steel Fish Tape - 65' × 1/8" (19.8 m × 3.2 mm) 3-PACK
FTS438-125	12709	Steel Fish Tape - 125' × 1/8" (38.1 m × 3.2 mm)
FTS438-125BP	10046	Steel Fish Tape - 125' × 1/8" (38.1 m × 3.2 mm) 3-PACK
FTS438-240	12730	Steel Fish Tape - 240' × 1/8" (73.2 m × 3.2 mm)
FTS438-240BP	10048	Steel Fish Tape - 240' × 1/8" (73.2 m × 3.2 mm) 3-PACK
FTS438W-100	12710	Steel Fish Tape - 100' × 1/4" (30.5 m × 6.4 mm)
S438W-200	12476	Steel Fish Tape - 200' × 1/4" (61 m × 6.4 mm)
RS438-65	12469	R Replacement Steel Tape - 65' (NO CASE)
RS438-125	12470	R Replacement Steel Tape - 125' (NO CASE)
RS438-240	12471	R Replacement Steel Tape - 240' (NO CASE)
RS438W-100	12472	R Replacement Steel Tape - 100' × 1/4" (NO CASE)
R438B	29367	A Swivel Ball Head for use on 1/8" Steel Fish Tapes
R438-BM	05853	A Ball Tip Male Half
439-1	30859	A 12" (305 mm) Flexible Fish Tape Leader
439-2	14392	A 12" (305 mm) SPEED FLEX Leader (solder joints)
10051	10051	R 8 1/2" Case/Handle Replacement Kit
10052	10052	R 12" Case/Handle Replacement Kit

SPECIFICATIONS

Capacity	1/8" (3.2 mm) tape width- 400 lbs. (1.7 kN) maximum design strength
	1/4" (6.4 mm) tape width - 400 lbs. (1.7 kN) maximum design strength.
	438-5H - 1/8" (3.2 mm) tape width- 400lbs. (1.7 kN) maximum design strength.
Weight	FTS438-65- 3.1 lbs. (1.4 kg) S438W-200 - 10.9 lbs. (4.9 kg)
	FTS438-125 - 5.5 lbs. (2.5 kg) 438-5H - 2.8 lbs. (1.3 kg)
	FTS438-240 - 8.5 lbs. (3.9 kg) 438-2X - 1.3 lbs. (.6 kg)
	FTS438W-100 - 7.2 lbs. (3.3 kg)

Fishing

INTERNATIONAL

Tel: +1.815.397.7070
Fax: +1.815.397.9247

CANADA

Tel: 800.435.0786
Fax: 800.524.2853

USA

Tel: 800.435.0786
Fax: 800.451.2632