

Metal Stud Punches



SPECIFICATIONS

Capacity

709 - 1-5/8" (41.3 mm) and wider studs. 20 gauge (0.9 mm) steel studs. 710 - 2-1/2" (63.4 mm) and wider studs. 20 gauge (0.9 mm) steel studs.

- Punch up through 20 gauge (0.9 mm) steel studs in one stroke.
- Aluminum head provides strength with minimum weight, reducing operator fatigue.
- Contoured handle design gives better operator leverage and makes it possible to punch in tight places.
- · Self-stripping design eliminates punch hang-ups.
- Automatically centers holes on standard studs.
- Conversion kit available to upgrade early models from 24 gauge to 20 gauge maximum capacity.

				WEIG	HT
	CAT NO.	UPC NO.	DESCRIPTION	LBS.	KG.
R	709	22280	7/8" (22.2 mm) Diameter Stud Punch	7	3.2
	710	21285	1-11/32" (34.1 mm) Diameter Stud Punch	7.5	3.5
	30968	30968	Conversion Kit – Upgrades Early Model 709 or 710 from 24 to 20 Gauge Maximum Capacity		
	121AV	04006	Punch for 709		
R	22286	22286	Die for 709		
R	24823	24823	Punch for 710		
R	21297	21297	Die for 710		
	06015	06015	Pin Kit		
	36617	36617	Link		
	05932	05932	Link and Pin Kit (709/710)		
	21557	21557	Compression Spring		

Bushings for Metal Stud Punches









- Triple lock design holds bushing securely.
- Locks securely into metal studs from 24 gauge to 12 gauge (0.6 mm to 2.5 mm).
- · Helps protect wire insulation from sharp edges of metal studs.
- Makes pulling smooth and easy by preventing hang-ups of cable on raw metal edges.

			WLIGH	
CAT NO.	UPC NO.	DESCRIPTION	LBS.	KG.
711C	22288	100 Bushings for Hole Punched by 709 for 7/8" (22.2 mm) Diameter Hole	.5	.23
711M	22289	1,000 Bushings for Hole Punched by 709 for 7/8" (22.2 mm) Diameter Hole	3.7	1.7
712A100	05927	100 Bushings for Pre-Punched Hole or 1-11/32" (34.1 mm) Diameter Hole Punched by 710	1.4	.64
712A1000	05928	1,000 Bushings for Pre-Punched Hole or 1-11/32" (34.1 mm) Diameter Hole Punched by 710	15.5	7.0

Manual Stud Punch



- Punch up through 20 gauge (0.9 mm) steel studs in one stroke.
- Unique patented punch rolls the edge over for smooth installation of armored cable; cable won't hang up.
- Contoured handle design gives better operator leverage and makes it possible to punch in tight places.
- · Automatically centers holes on standard studs.

	CAT NO.	UPC NO.	DESCRIPTION
	724	10415	Manual Stud Punch
R	10419	10419	Punch for 724

SPECIFICATIONS

Actual Hole Size 1-1/4" (31.7 mm)
Weight 4.0 lbs. (1.8 kg)
Length 16-3/4" (426 mm)
Height 4-1/2" (247 mm)
Capacity 24-20 GA (0.9 mm)

WFIGHT