





































Reciprocating Saw Blades

		LENGTH X WIDTH X THICKNESS							
MATERIAL	APPLICATION	TPI	INCH	MM	CAT. NO.	UPC NO.		QTY. PER PK.	
GREENLEE - BI-METAL									
METAL 	For cutting thick metal 1/8" - 1/2"	10/14T	8 x 3/4 x .050	203 x 19 x 1.3	353-804	09977		5	
	For cutting thick metal 3/32" - 3/8"	14T	4 x 3/4 .035	102 x 19 x .9	353-414	01031		5	
		14T	6 x 3/4 x .035	152 x 19 x .9	353-614	09964		5	
		14T	8 x 3/4 x .050	203 x 19 x 1.3	353-814	09975		5	
	For cutting medium metal 1/16" - 3/16"	18T	6 x 3/4 x .035	152 x 19 x .9	353-618	09965		5	
		18T	8 x 3/4 x .035	203 x 19 x .9	353-818	09976		5	
		18T	8 x 3/4 x .050	203 x 19 x 1.3	353-818T	13004		5	
	For cutting thin metal 1/8" and less.	24T	6 x 3/4 x .035	152 x 19 x .9	353-624	09966		5	
	GENERAL PURPOSE 	General purpose blade for cutting metal, wood w/ nails, and PVC.	8/18T	6 x 3/4 x .035	152 x 19 x .9	353-123	09963		5
			10T	6 x 3/4 x .035	152 x 19 x .9	353-610	31366		5
10T			8 x 3/4 x .050	203 x 19 x 1.3	353-810	31337		5	
10/14T			12 x 3/4 x .050	305 x 19 x 1.3	353-110	31338		5	
10/14T			6 x 3/4 x .035	152 x 19 x .9	353-635	01020		5	
10/14T			8 x 3/4 x .035	203 x 19 x .9	353-835	01022		5	
DEMOLITION 			For cutting a wide variety of construction materials during demolition or remodeling.	5/8T	9 x 7/8 x .063	229 x 22 x 1.6	353-966	09979	
	8/10T	9 x 7/8 x .063		229 x 22 x 1.6	353-969	09990		5	
WOOD 	For cutting in clean wood and wood w/ nails.	5/8T	6 x 3/4 x .050	152 x 19 x 1.3	353-503	13005		5	
		6T	6 x 3/4 x .050	152 x 19 x 1.3	353-646	09968		5	
		6T	6 x 3/4 x .050	153 x 19 x 1.3	353-656	09967		5	
		6T	9 x 3/4 x .050	229 x 19 x 1.3	353-956	09969		5	
		6T	12 x 3/4 x .050	305 x 19 x 1.3	353-156	09970		5	
GREENLEE - SPECIALTY									
DRYWALL 	For fast cutting in drywall and plaster.	6T	6 x 3/4 x .050	152 x 19 x 1.3	353-636	31336		5	
CEMENT BOARD 	For fast cutting in cement board, fiber board, and plaster.	3T	9 x 3/4 x .050	229 x 19 x 1.3	353-9535RCT	00964		1	
		6T	6 x 3/4 x .050	152 x 19 x 1.3	353-6563RCT	00963		1	
CAST IRON & BLOCK 	For cutting cast iron pipe, block & brick and other abrasives such as tile.	Diamond Grit	8 x 3/4 x .039	203 x 19 x 1	353-800RDG	01024		1	
		Carbide Grit	9 x 3/4 x .039	229 x 19 x 1	353-900RG	01023		1	
STAINLESS STEEL 	For cutting stainless steel 1/16" - 3/16"	18T	6 x 3/4 x .039	152 x 19 x 1	353-618RS	01047		1	