



# GFCIs

## PlugTail™ Hospital Grade Self-Test GFCI Receptacles with SafeLock™ Protection 2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



**PT2097HGW**



**PTRA6STR**



### Features

- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3-wire PlugTail Connectors creating a non-feed-thru application for facility owners.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box.
- Auto-Ground clip assures a positive ground to metal box.
- Meets 2015 UL requirements.
- 10kA short circuit rating.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL 943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trio Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	VAC			UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>HOSPITAL GRADE 15 AMP DUPLEX GFCI</b>							
PT1597HGI	15	125	Ivory	5-15R	•	•	•
PT1597HGW	15	125	White	5-15R	•	•	•
PT1597HGBK	15	125	Black	5-15R	•	•	•
PT1597HGRED	15	125	Red	5-15R	•	•	•
PT1597HGLA	15	125	Light Almond	5-15R	•	•	•
<b>HOSPITAL GRADE 20 AMP DUPLEX GFCI</b>							
PT2097HGI	20	125	Ivory	5-20R	•	•	•
PT2097HGW	20	125	White	5-20R	•	•	•
PT2097HG	20	125	Brown	5-20R	•	•	•
PT2097HGGRY	20	125	Gray	5-20R	•	•	•
PT2097HGBK	20	125	Black	5-20R	•	•	•
PT2097HGRED	20	125	Red	5-20R	•	•	•
PT2097HGLA	20	125	Light Almond	5-20R	•	•	•



CATALOG NUMBER	WIRE TYPE	WIRE LENGTH
<b>PLUGTAIL CONNECTORS – RIGHT ANGLE</b>		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"

For additional PlugTail Connectors, see Page B-4.

All PlugTail Connectors are available in any wire length up to 25 inches, consult factory to order.

All devices listed on this page conform to NEMA WD-1 and WD-6.