



BURNDY Catalog Number YAL28T12
UPC Number 78181041707
Description CANLUG-4/0 STR-SHORT-1/2
Status null

Web Use
BURNDY Product Line

Dimensional

Tongue Angle Straight
Length (in) 2.24
Tongue Type Standard
Barrell Style Chamfered
Bolt Hole Size (in) 0.52
Barrel Type Standard
Thickness 0.14
B Length (in) 0.78
Pad Width (in) 1.02

General

Number of Holes 1

Conductor(s)

Copper Stranded (Range) 4/0
Copper Solid Size (Range) N/A

Physical

Type of Plating Tin - Electro Plated
Color Code Purple
Plated (Yes or No) Y
Index Number 15
Product Material Copper

Approvals / Certifications

Industry Standards UL468A-468B
UL Listed Yes,Y
CSA Certified Yes,Y
ROHS Compatible Compliant
UL Recognized N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA
47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services
47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175