Kits and Accessories

Type P2 Panelboards

Table P2-20 – Standard Enclosures

Box Height Inches	Catalog Number					
	Type 1 Standard Trim			Type 3R	Type 3R/12	
	Box	Surface	Flush			
26	B26	S26B	F26B	NR26	WP26	
32	B32	S32B	F32B	NR32	WP32	
38	B38	S38B	F38B	NR38	WP38	
44	B44	S44B	F44B	NR44	WP44	
50	B50	S50B	F50B	NR50	WP50	
56	B56	S56B	F56B	NR56	WP56	
62	B62	S62B	F62B	NR62	WP62	
68	B68	S68B	F68B	NR68	WP68	
74	B74	S74B	F74B	NR74	WP74	

Options For Type 1 Trims

Items must be ordered as manual line item on Spartanburg Hinged trim – Replace "B" suffix with "H" Door-in-door – Replace "B" suffix with "D" Metal card holder – Replace "B" suffix with "M" on standard trim, add "M" suffix on optional trims

Option For 24" Wide Enclosures with Equal Gutter on Both Sides

24" wide with equal gutter on both sides - Add "24" as prefix

Table P2-21 – Breaker Kits and Accessories

Kit No.	Description	Contents		
BBKB32	BL/BQD 6-pole 3" branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware		
BBKED32	ED 6-pole 3" branch breaker kit	Kit contains breaker support, inter-phase barriers, (3) A/C connectors, (1) B connector, hardware		
BBKQ1	QJ branch breaker kit for 2 and 3-pole single mount	Kit to contain all connectors and cover plates necessary to mount both 2 and 3-pole breakers		
DFK1	BL, BQD, ED deadfront kit for 1" pole breakers	Center strips 3", 6", 9," 15," 21" plus mounting hardware		
DFFP3	Deadfront filler 3"	3" empty space filler and hardware		
DFFP6	Deadfront filler 6"	6" empty space filler and hardware		
BNK2	Branch neutral (P2)	Three tier lug with mounting hardware to increase neutral capacity		
P2BK1	P2 250A max. Bonding Kit	Bonding strap and hardware		
P2BK2	P2 400A max. Bonding Kit	Bonding strap and hardware		
P2BK3	P2 600A max. Bonding Kit	Bonding strap and hardware		