

TWO-DOOR WITH FLOOR STANDS, TYPE 12

INDUSTRY STANDARDS

 UL 508A Listed; Type 12; File No. E61997
 cUL Listed per CSA C22.2 No. 94; Type 12; File No. E61997

 NEMA/EEMAC Type 12
 CSA, File No. 42186, Type 12
 IEC 60529, IP55

APPLICATION

Enclosures have gasketed, overlapping doors to keep the elements at bay and floor stands that provide additional height and access for cleaning under the enclosure. Because there is no centerpost, it is simple to install and remove panels.

SPECIFICATIONS

- Seams continuously welded and ground smooth; no holes or knockouts
- Gasketed overlapping doors with no centerpost
- 3-point latch mechanism operated by oil-tight key-lock handle
- Latch rod rollers for easy door closing
- Concealed, easy-to-remove hinges
- Data pocket is high-impact thermoplastic
- 12-in. floor stands welded to enclosure
- Heavy-duty lifting eyes
- Panel supports
- Oil-resistant gasket
- Collar studs for mounting optional panel
- Bonding provision on door
- Provision for mounting fluorescent light

FINISH

Two finishes available: ANSI 61 gray, polyester powder paint outside and inside; or ANSI 61 gray outside and white, polyester powder paint inside. Optional panels available with a white or conductive finish.

ACCESSORIES

See also *Accessories*.
 Blower Fan Package
 Drip Shield Kit for Type 12 Enclosures
 INTERSAFE™ Data Interface Ports, Type 4/4X/12
 PANELITE™ Enclosure Lights Overview

MODIFICATION AND CUSTOMIZATION

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

BULLETIN: A12L

Standard Product

Catalog Number	AxBxC in.	AxBxC mm	Interior Finish	Gauge	Panel	Conductive Panel	Panel Gauge	Panel Size (in.)	Panel Size (mm)	Stiffener (in.)	Stiffener (mm)	S (in.)	S (mm)
A544208LPG	54.00 x 42.00 x 8.00	1372 x 1067 x 203	Gray	12	A54P42	A54P42G	12	50.00 x 38.00	1270 x 965	15.00	381	—	—
A544208LP	54.00 x 42.00 x 8.00	1372 x 1067 x 203	White	12	A54P42	A54P42G	12	50.00 x 38.00	1270 x 965	15.00	381	—	—
A604808LPG	60.06 x 48.06 x 8.06	1526 x 1221 x 205	Gray	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604808LP	60.06 x 48.06 x 8.06	1526 x 1221 x 205	White	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604810LPG	60.06 x 48.06 x 10.06	1526 x 1221 x 256	Gray	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604810LP	60.06 x 48.06 x 10.06	1526 x 1221 x 256	White	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A606010LPG	60.06 x 60.06 x 10.06	1526 x 1526 x 256	Gray	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A606010LP	60.06 x 60.06 x 10.06	1526 x 1526 x 256	White	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A726010ULPG	72.06 x 60.06 x 10.06	1830 x 1526 x 256	Gray	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A726010ULP	72.06 x 60.06 x 10.06	1830 x 1526 x 256	White	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A727210ULPG	72.06 x 72.06 x 10.06	1830 x 1830 x 256	Gray	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A727210ULP	72.06 x 72.06 x 10.06	1830 x 1830 x 256	White	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A604812LPG	60.06 x 48.06 x 12.06	1526 x 1221 x 306	Gray	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604812LP	60.06 x 48.06 x 12.06	1526 x 1221 x 306	White	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A606012LPG	60.06 x 60.06 x 12.06	1526 x 1526 x 306	Gray	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A606012LP	60.06 x 60.06 x 12.06	1526 x 1526 x 306	White	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A726012ULPG	72.06 x 60.06 x 12.06	1830 x 1526 x 306	Gray	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A726012ULP	72.06 x 60.06 x 12.06	1830 x 1526 x 306	White	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A727212ULPG	72.06 x 72.06 x 12.06	1830 x 1830 x 306	Gray	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A727212ULP	72.06 x 72.06 x 12.06	1830 x 1830 x 306	White	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608

Catalog Number	AxBxC in.	AxBxC mm	Interior Finish	Gauge	Panel	Conductive Panel	Panel Gauge	Panel Size (in.)	Panel Size (mm)	Stiffener (in.)	Stiffener (mm)	S (in.)	S (mm)
A604816LPG	60.06 x 48.06 x 16.06	1526 x 1221 x 408	Gray	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604816LP	60.06 x 48.06 x 16.06	1526 x 1221 x 408	White	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A606016LPG	60.06 x 60.06 x 16.06	1526 x 1526 x 408	Gray	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A606016LP	60.06 x 60.06 x 16.06	1526 x 1526 x 408	White	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A726016LPG	72.06 x 60.06 x 16.06	1830 x 1526 x 408	Gray	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A726016LP	72.06 x 60.06 x 16.06	1830 x 1526 x 408	White	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A727216LPG	72.06 x 72.06 x 16.06	1830 x 1830 x 408	Gray	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A727216LP	72.06 x 72.06 x 16.06	1830 x 1830 x 408	White	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A604820LPG	60.06 x 48.06 x 20.06	1526 x 1221 x 510	Gray	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604820LP	60.06 x 48.06 x 20.06	1526 x 1221 x 510	White	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A726020LPG	72.06 x 60.06 x 20.06	1830 x 1526 x 510	Gray	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A726020LP	72.06 x 60.06 x 20.06	1830 x 1526 x 510	White	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A727220LPG	72.06 x 72.06 x 20.06	1830 x 1830 x 510	Gray	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A727220LP	72.06 x 72.06 x 20.06	1830 x 1830 x 510	White	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A604824LPG	60.06 x 48.06 x 24.06	1526 x 1221 x 611	Gray	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A604824LP	60.06 x 48.06 x 24.06	1526 x 1221 x 611	White	12	A60P48	A60P48G	10	56.00 x 44.00	1422 x 1118	15.00	381	15.92	404
A606024LPG	60.06 x 60.06 x 24.06	1526 x 1526 x 611	Gray	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A606024LP	60.06 x 60.06 x 24.06	1526 x 1526 x 611	White	12	A60P60	A60P60G	10	56.00 x 56.00	1422 x 1422	21.00	533	19.92	506
A726024LPG	72.06 x 60.06 x 24.06	1830 x 1526 x 611	Gray	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A726024LP	72.06 x 60.06 x 24.06	1830 x 1526 x 611	White	12	A72P60	A72P60G	10	68.00 x 56.00	1727 x 1422	21.00	533	19.92	506
A727224LPG	72.06 x 72.06 x 24.06	1830 x 1830 x 611	Gray	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608
A727224LP	72.06 x 72.06 x 24.06	1830 x 1830 x 611	White	12	A72P72	A72P72G	10	68.00 x 68.00	1727 x 1727	24.00	610	23.92	608

Purchase panels separately.

