

Standard 7-Day Programmable Timers - 15 A

EI500 Series

For installation on 15 A circuits, this timer provides 24-hour or 7-day programming of lights, fans, pumps and other medium-duty loads.

Features

- 7-day programmable schedules with 14 ON/OFF events
- Automatic Daylight Saving Time (DST) adjustment
- Random mode varies ON/OFF schedule to provide a "lived-in" appearance
- Single pole circuit
- Incandescent/fluorescent/CFL/LED compatible
- Built-in rechargeable, non-serviceable battery backup
- Requires neutral connection

White	Ivory	Light Almond
EI500WC	EI500C	EI500LAC

Note: For use with a standard decorator plate, not included.



White



Ivory



Light Almond



EI500LAC



Ratings	
Operating Voltage	125 VAC, 60 Hz
General Purpose	15 A
Resistive	15 A
Inductive Ballast (Fluorescent)	1000 VA
Electronic/LED Ballast	500 VA
Incandescent	1000 W
Motor	¼ HP
Operating Temperature	32° F to 104° F (0° C to 40° C)
Dimensions H x W x D	4 ½" x 1 ¾" x 1 ⅞" (104.8 mm x 44.5 mm x 36.5 mm)
Warranty	1-year limited

Note: Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

Standard 7-Day Programmable Timers - 12 A

EJ600 Series

A 12 A rated timer that provides full 7-day programming capabilities with dusk-to-dawn functionality, ideal for use with medium to low power loads.

Features

- 7-day programmable schedules with 14 ON/OFF events
- Astronomic clock feature determines dawn and dusk times
- Automatic Daylight Saving Time (DST) adjustment
- Random mode varies ON/OFF schedule to provide a "lived-in" appearance
- Single or 3-way switch compatible installation
- Incandescent/fluorescent/CFL/LED compatible
- Built-in rechargeable, non-serviceable battery backup
- Requires neutral connection

White	Light Almond
EJ600	EJ600A

Note: For use with a standard decorator plate, not included.



White



Light Almond



EJ600



Ratings	
Operating Voltage	120 VAC, 60 Hz
Resistive	12 A, 120 VAC
Inductive Ballast (Fluorescent)	500 VA
Incandescent	
Single-Gang	15 A, 120 VAC
Multi-Gang	12 A, 120 VAC
Motor	½ HP
Operating Temperature	32° F to 104° F (0° C to 40° C)
Dimensions H x W x D	4 ½" x 1 ¾" x 1 ⅞" (104.8 mm x 44.5 mm x 36.5 mm)
Warranty	1-year limited

Note: Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.