

Code•Master™ Jr. HID Factory Sealed Luminaires





Explosionproof, Dust-Ignitionproof

Integrally Ballasted. 50 W, 70 W, 100 W, 150 W HPS; 50 W, 70 W, 100 W, 175 W PSMH. 175 W MH. Medium Base. For Use with Threaded Metal Conduit.

NEC:
Class I, Division 1 and 2, Groups B♦, C, D
Class II, Division 1 and 2, Groups E, F, G
Class III
Marine type electric fixtures, outside type
(salt water)

CEC:
Class I, Division 1 and 2, Groups B♦, C, D
Class II, Division 1 and 2, Groups E, F, G
Class III
Type 4X
Exd IIB + H₂

Mounting Hoods

	Hub Size (Inches)	Catalog Number
Pendant — One Hub		
	3/4	CAP-75
	1 ②	CAP-100
Ceiling — Four Hubs, Three Close-Up Plugs		
	3/4	CAC-75
	1 ②	CAC-100
Bracket — Four Hubs, Three Close-Up Plugs		
	3/4	CALB-75
	1 ②	CALB-100
25° Stanchion — One Hub		
	1-1/4 or 1-1/2 ①	CAS-150

Mounting Adapter with Connection Block



Permits use of existing A-51 mounting hoods (AAC Ceiling or AALB Bracket) with the new Code•Master 2 Fixture Unit. After removing existing fixture unit and adapter, screw in the new CMAD-1 Adapter. Then thread new fixture unit into the CMAD-1.

CMAD-1

Fixture Units

Ballast body with globe. Indicate voltage desired by adding voltage suffix to fixture unit catalog number listed below.

Type	Lamp Watts	Fixture Unit Number	Add Voltage Suffixes		
			120/208/240/277	120/277/347 ④	480 V
High Pressure Sodium ③ High Power Factor (Min. P.F. 90%)	50	CJB50L-	MT	TTCN	—
	70	CJB70L-	MT	TTCN	48
	100	CJB100L-	MT	TTCN	48
	150	CJB150L-	MT	TTCN	48
Pulse Start Metal Halide Constant Wattage (Min. P.F. 90%)	50	CJB50H-	MT	TTCN	—
	70	CJB70H-	MT	TTCN	48
	100	CJB100H-	MT	TTCN	48
	175	CJB175P-	MT	TTCN	48
Metal Halide Constant Wattage (Min. P.F. 90%)	175	CJB175H-	MT	TT	C6

① 1-1/2" Tapped hub furnished with 1-1/2" to 1-1/4" reducer.

② Mounting Hoods with 1" hub listed for Class I, Group D; Class II, Groups E,F,G; and Class III only.

③ Add suffix **-R** for "Hot Restrike" and **-S** for "Smart Starter" options.

④ Change voltage suffix **-TTCN** to **-MTCN** for 120/208/240/277 V, **-C2** for 208 V, **-C3** for 240 V, **-C6** for 480 V, or **-C7** for 600 V. These voltage suffixes have CSA Certification only.

⑤ Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.

◆ Shaded area indicates items suitable for Class I, Division 1, Group B.

HID/AREA: NEC/CEC EXPLOSIONPROOF

Appleton®