



**BURNDY Catalog Number** YAL27T12  
**UPC Number** 78181041703  
**Description** CANLUG-3/0 STR-SHORT-1/2  
**Status** null

**Web Use**  
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.22
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.13
B Length (in)	0.79
Pad Width (in)	0.91
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	3/0
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Orange
Plated (Yes or No)	Y
Index Number	14
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**  
 47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**  
 47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175