



BURNDY Catalog Number	YAL6C2T38
UPC Number	78181041756
Description	CANLUG- 6STR-SHORT-3/8X1
Status	null

Web Use
BURNDY Product Line

	Dimensional
Tongue Angle	Straight
Length (in)	2.74
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.06
B Length (in)	0.75
Pad Width (in)	0.56
E - in	1
	General
Number of Holes	2
	Conductor(s)
Copper Solid Size (Range)	6
Copper Stranded (Range)	6
	Physical
Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7
Product Material	Copper
	Approvals / Certifications
Industry Standards	UL468A-468B
UL Listed	Yes,Y
CSA Certified	Yes,Y
ROHS Compatible	Compliant
UL Recognized	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services
47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175