

The Marrette® Set-Screw is a two-piece, pressure type connector, featuring a solid brass insert with a screw-on insulating cap. It's the perfect choice when changing a motor, adding a circuit, conducting instrument testing or simply lashing-up temporary wiring.


External Cap

- Made of rugged, phenolic material 150°C rated.
- Insulator cap locks securely in place to safeguard against accidental loosening in high vibration applications.

Inner Sleeve + Screw

- Choice of Slotted or Robertson screw-driver installation. When tightened into the insert, provides a solid pressure type connection on all approved wire combinations.
- No need to "re-strip" wires when rewiring. Simply loosen set screw to remove non-twisted wires.
- Brass sleeve + set-screw help resist corrosion.
- Approved for circuits up to 600V, and lighting fixtures and signs up to 1000V.
- · For copper conductor only.
- · Convenient packaging sized right and job-site ready!











Specifications



Ordering Information

| | | | | AWG Wir | e Range | | |
|------------|---|-------------|-------------|-----------|------------|----|---|
| Cat. No. | Description | 18 | 16 | 14 | 12 | 10 | 8 |
| 1SHD, 1SHP | Cap and insert combination screw & brass barrel | Min.: 2 #18 | Max.: 1 #1 | 8 + 3 #14 | | | |
| 1SHi | Insert screw & brass barrel only | Min.: 2 #18 | Max.: 1 #1 | 8 + 3 #14 | | | |
| 2SHD, 2SHP | Cap and insert combination screw & brass barrel | | Min.: 2 #14 | Max.: 1 # | 12 + 2 #10 | | |
| 2SHi | Insert screw & brass barrel only | | Min.: 2 #14 | Max.: 1 # | 12 + 2 #10 | | |

Note: Refer to pages 22 and 23 for related Wire Combination Reference Guides.

Packaging Options

| | Catalogue Number | Packaging Format | Quantity per Package | Std. Pkg. |
|-----|------------------|------------------|----------------------|-------------|
| 1SH | 1SHP | Propak | 100 | 1,000 Units |
| | 1SHD | Flip-Pak | 500 | 500 Units |
| | 1SHi | Carton | 100 | 1,000 Units |
| 2SH | 2SHP | Propak | 50 | 500 Units |
| | 2SHD | Flip-Pak | 500 | 500 Units |
| | 2SHi | Carton | 50 | 1,000 Units |





Small Formats

| Model | Format | Description |
|-------|------------|---|
| C | Card | Blistercard of 3, 6, 15 or 20 (Retail market only) |
| B | Window Box | Small box of 15, 25 or 50 (Retail market only) |
| P | Propak | Box of 50 or 100 |









Bulk Pack Formats

| Model | Format | Description |
|-------|---------------|---|
| Q | Flip-Pak | Container of 200 or 250 |
| MFP | Mini Flip-Pak | Container of 200 to 500 (Retail market only) |
| D | Flip-Pak | Container of 500 |
| М | Flip-Pak | Container of 1,000 |
| BP | Box | Bulk box of 1,000 |
| BK | Flip-Pak | Bulk keg of 5,000 to 10,000 (depending on model) |
| BAR | Barrel | Barrel of 20,000 to 45,000 (depending on model) - included: 3 unmarked Flip-Paks (500 marrettes format) with lids |



Bag Formats

| Model | Format | Description |
|-------|---------|------------------------------|
| KP | Keg Pak | Resealable bag of 250 or 500 |

