



BURNDY Catalog Number YAV4T38B
UPC Number 7818104256577
Description CANLUG- 4 FLEX-3/8-BELL
Status Active

Web Use
 BURNDY Product Line

Dimensional
 Tongue Angle Straight
 Length (in) 1.76
 Barrell Style Belled
 Bolt Hole Size (in) 0.39
 Barrel Type Standard
 Thickness 0.11
 B Length (in) 0.68
 Pad Width (in) 0.60

General
 Number of Holes 1
 Product Description Pure Electrolytic Seamless Cu
 Tube Compression Terminal, 1
 Hole W/InspWindow, #4 AWG
 Flex, 3/8" Stud, Belled End

Conductor(s)
 Aircraft Cable Size (Range) N/A
 Flex (Class H) Size - Range 4 AWG
 Flex (Class I) Size - Range 4 AWG
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Navy Cable Size (Range) N/A
 Copper Stranded (Range) N/A
 Flex (Class G) Size - Range 4 AWG
 Flex (Class M) Size - Range 4 AWG

Physical
 Type of Plating Tin - Electro Plated
 Bolt Hole Size 3/8
 Plated (Yes or No) Y
 Product Material Copper

Approvals / Certifications
 UL Listed N
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175