

Panelboards

Type P2 Panelboard Connector Modifications

Selection

Enclosure Modifications

Description	List Price Adder \$	
	Panel Width 20"	Panel Width 24"
NEMA 3R enclosure s	760.	1045.
NEMA 3R/12 enclosure s	760.	1045.
Gasket between trim and box (Type 1)	600.	795.

NEMA-4 for Type P2 Water Tight, Dust Tight, Steel Enclosure (consult plant for actual enclosure size)

Box Height Inches	Enclosure Size			List Price Adder \$
	H	W	D	
26	26	20	5.75	3470.
32	32	20	5.75	3750.
38	38	20	5.75	4725.
44	44	20	5.75	5850.
50	50	20	5.75	7100.
56	56	20	5.75	14400.
62	62	20	5.75	18200.
68	68	20	5.75	22000.
74	74	20	5.75	25990.

NEMA-4X for Type P2 Water Tight, Dust Tight and Corrosion Resistant (consult plant for actual enclosure size)

Box Height Inches	Enclosure - Stainless Steel and Steel with Epoxy Coating			Enclosure - Fiberglass Size (inches)			List Price \$
	H	W	D	H	W	D	
26	26	20	5.75	30	24	8	7975.
32	32	20	5.75	36	24	8	8990.
38	38	20	5.75	48	36	12	10700.
44	44	20	5.75	48	36	12	14000.
50	50	20	5.75	60	36	12	16570.
56	56	20	5.75	60	36	12	17950.
62	62	20	5.75	72	36	8	21000.
68	68	20	5.75	72	36	8	24300.
74	74	20	5.75	84	36	8	27600.

Remote Switch Modifications (see page 10-68)

Application For Remote Switch

Switch Type	Modification
920	Adds 12" to unit space
911	≤ 225A Adds 21" unit space >225 ≤400 Amps Add 10" to width and 8" DP minimum and 24" to height
LEN	30A Adds 15" to unit space >30A 100 Adds 12" to unit space 7.7 Dp. Box min. 100 A ≤ 200 Adds 12" to unit space and 10" Dp. min.

Panelboards

Type P2 Panelboard Kits and Accessories

Accessories

Standard Enclosures

Box Height Inches	Catalog Number					
	Type 1	Standard Trim			Type 3R	Type 3R/12
	Box	Surface	Flush			
26	B26	S26B	F26B	NR26	WP26	
32	B32	S32B	F32B	NR32	WP32	
38	B38	S38B	F38B	NR38	WP38	
44	B44	S44B	F44B	NR44	WP44	
50	B50	S50B	F50B	NR50	WP50	
56	B56	S56B	F56B	NR56	WP56	
62	B62	S62B	F62B	NR62	WP62	
68	B68	S68B	F68B	NR68	WP68	
74	B74	S74B	F74B	NR74	WP74	

Options For Type 1 Trims

Items must be ordered as manual line item on Spartanburg

Hinged trim – Replace “B” suffix with “H”

Door-in-door – Replace “B” suffix with “D”

Metal card holder – Replace “B” suffix with “M” on standard trim, add “M” suffix on optional trims

Option For 24” Wide Enclosures with Equal Gutter on Both Sides

24” wide with equal gutter on both sides - Add “24” as prefix

Breaker Kits and Accessories

Kit Number	Description	Contents	List Price \$
BBKB32	BL/BQD 6-pole 3” branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware	75.
BBKED32	ED 6-pole 3” branch breaker kit	Kit contains breaker support, inter-phase barriers, (3) A/C connectors, (1) B connector, hardware	80.
BBKQ1	QJ branch breaker kit for 2- and 3-pole single mount	Kit to contain all connectors and cover plates necessary to mount both 2- and 3-pole breakers	90.
DFK1	BL, BQD, ED deadfront kit for 1” pole breakers	Center strips 3”, 6”, 9”, 15”, 21” plus mounting hardware	80.
DFFP3	Deadfront filler 3”	3” empty space filler and hardware	40.
DFFP6	Deadfront filler 6”	6” empty space filler and hardware	45.
BNK2	Branch neutral (P2)	Three tier lug with mounting hardware to increase neutral capacity	40.
P2BK1	P2 250A max. Bonding Kit	Bonding strap and hardware	20.
P2BK2	P2 400A max. Bonding Kit	Bonding strap and hardware	20.
P2BK3	P2 600A max. Bonding Kit	Bonding strap and hardware	20.