

Grounding

Ground Rod Clamps



CI3106



CI3108



CI3110U



CI3112U



Cat. No.	Water Pipe Size (in.)	Dimensions (in.)		Galv. Steel (in.)	Copper Clad (in.)
		Min.	Max.		
Ground Clamps (Zinc alloy body / Steel screws)					
CI3106	1/2 to 1	10 sol.	2 str.	5/8 to 1 *	N/A
Ground Clamps (Zinc / Steel)					
CI3108	1/2 to 1	10 sol.	2 str.	5/8 to 1 *	N/A
For connecting grounding conductor to either galvanized steel rod or water pipe.					
Ground Clamps (Brass body / brass screws)					
CI3110U	1/2 to 1	10 sol.	2 str.	5/8 to 1 *	5/8 to 1
For connecting grounding conductor to either galvanized steel rod, copper clad rod or water pipe. CSA certified for wet locations and for direct burial.					
Ground Clamps (Brass body / brass screws)					
CI3112U	1-1/4 to 2	10 sol.	2 str.	—	—
For connecting grounding conductor to water pipe CSA certified for wet locations and for direct burial					
* Reversible					