

## **Device Boxes**

## **Armoured and Nonmetallic Sheathed Cable Clamps**



BC3104-LH

Positioning tabs. Provision for external nailing.



BC3104-LHTQ

One screw mounting. Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.



BC3104-LSSX

"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.



CI3104-LSS1X-1

"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.



CI1804-LH

Positioning tabs. External nailing. Mounting slots for internal screw installation. X-Cube adds 5.5 cu. in.



BC2004-LH

Provision for external nailing. Holding prongs and prepositioned depth tabs on one side.



## BC2004-LHTQ

Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.



## CI2016-LX

Self-locking spring clamps. Holding prongs and prepositioned depth tabs on one side. **Approved for nonmetallic sheathed cable only.** 



Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
2-1/2 in. Deep — Gangable — 3	in. x 2 in.			
BC3104-LH	16.0	-	P. Tabs	4
BC3104-LHTQ	16.0	-	P. Tabs	4
BC3104-LSSX	16.0	-	"SSX"	4
CI3104-LSS1X-1	16.0	-	"SSX"	4
CI1804-LH	18.0	-	P. Tabs	4
2-3/4 in. Deep — Non-Gangable	3-3/4 in.	x 2-3/16 in.		
BC2004-LH	18.5	-	P. Tabs	4
BC2004-LHTQ	20.5	-	P. Tabs	4
2-1/2 in. Deep — Non-Gangable	— 3-3/4 in.	x 2 in.		
CI2016-LX	18.5	-	P. Tabs	4

