# **Cable Cutters**

### **Utility Cable Cutter**

- Forged steel with black-oxide finish for long life.
- Shear-type hook jaws grab and hold while shear-cutting action makes cle
- Beveled tips for positive mating.
- Hinge bolt with pin-set nut for prop
- Non-slip vinyl grips.
- Not designed for cutting steel or ACSR.

h Id cable lean cuts.	
per blade tension.	
CSR	63035

Cat. No.	Overall Length	MCM Cable-Cutting Maximum Capacity	Handle Color	Weight (lbs.)
63035	16-3/4" (425 mm)	350 copper, 350 aluminum	red	1.70

#### **Standard Cable Cutters**

- Lightweight, yet efficient shear-type cable cutters.
- Replaceable hook-jaw blades grab and hold cable while shear-cutting action makes clean cuts.
- Exceptionally strong fiberglass handles with heavy vinyl grips for comfort and slip resistance.
- Heavy-duty pins in head serve as blade-stops.
- Jaws are forged tool steel with black-oxide finish for long life.
- Beveled tips assure positive mating, and hinge on a rugged bolt with a pin-set nut to maintain proper blade tension.
- Makes a clean, even cut for ease in fitting lugs and terminals.
- Not designed for cutting steel or ACSR.

Cat. No.	Overall Length	Soft Cable-Cutting Maximum Capacity	MCM Cable-Cutting Maximum Capacity	Weight (lbs.)	
63041	25-1/2" (648 mm)	1-3/8" (35 mm) diameter	500 copper, 750 aluminum	5.25	
63045	32" (813 mm)	1-3/4" (44 mm) diameter	1000 copper, 1200 aluminum	8.00	
Replacement Cable Cutter Heads (complete)			Fits Klein Cat. No.		
63081			63041	2.05	
63090			63045	3.30	

#### **Communications Cable Cutter**



- Klein Standard Cable Cutters, but will cut lead or rubber-covered communications cable.
- Not designed for cutting steel or ACSR.

Cat. No.	Overall Length	Communications Cable-Cutting Maximum Capacity	Soft Cable-Cutting Maximum Capacity	Weight (lbs.)
63047	37" (940 mm)	900-pair soft copper and aluminum	up to 2-1/4" (57 mm) diameter	8.55
Replacen	nent Cable Cuti	ter Heads (complete)	Fits Klein Cat. No.	
63110			63047	3.50

All dimensions are in inches and (millimeters).

**AWARNING:** Do NOT use to cut steel or ACSR.

**AWARNING:** Always wear approved eye protection.

**AWARNING:** NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

63041


**Cable & Bolt Cutters** 



50

## **Cable Cutters**

#### Features:



Additional Features:

- High-leverage design for exceptional cutting capability.
- Precision, one-hand shearing action.
- Cable-gripping shear-type jaws.
- Perfect for working in confined spaces.
- Can be carried in most tool pouches.



**AWARNING:** Do NOT use to cut steel or ACSR.

Cat. No.	Overall Length	Handle Color	Handle Color Maximum Cable Cutting Capacity			
63050	9-1/2" (241 mm)	red	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications wire	.90		
Journeyman Series – Dual-material handles						
J63050	9-3/4" (248 mm)	red and black	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications wire	.98		

### Multi-Cable Cutter KLEIN-KURVE®

- Hardened steel precision-ground cutting blades for long life.
- Copper curved cutter cleanly cuts round copper cable without compression or frayed ends.
- Anvil cutter for solid and stranded copper wire up to 12 AWG and stainless steel up to .032" (.81 mm) diameter.
- Mild steel cutter for conductors up to .080" (2 mm) diameter.
- Curved cutter for solid and stranded copper wire up to 8 AWG, multi-conductor cable up to 1/2" (13 mm) diameter and coaxial cable RG-6 Quad, RG-59, and RG-62.
- Double-dipped grips for comfort.
- Coil spring provides fast self-opening action.
- Holes for looping and bending wire.
- Handy closure lock for convenient storage.



Cat. No.	Overall Length	Screw Shearing	Handle Color	Weight (lbs.)
63020	7" (177 mm)	6-32 & 8-32	red	.44

All dimensions are in inches and (millimeters).

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

48