

Mid-Size Parts Storage Boxes & Slide Racks

Slide Racks

- Holds Klein mid-size storage boxes.
- Boxes not included with rack, must be ordered separately.
- Welded, extra-rigid, all-steel construction.
- Metallic-gray, baked-enamel finish.
- Boxes ride in and out on heavy-duty channel tracks that permit covers to open all the way for full access.
- Heavy tabs prevent boxes from being accidentally pulled out, yet allow boxes to be easily removed when desired.
- Locking bars can be readily attached to prevent unauthorized access.

Cat. No.	Holds	Length (Front to Back)	Width	Height	Weight (lbs.)
54474	4 Klein mid-size storage boxes	11-3/4" (298 mm)	15-1/4" (387 mm)	10-3/4" (273 mm)	20.30
54476	6 Klein mid-size storage boxes	11-3/4" (298 mm)	15-1/4" (387 mm)	16-3/8" (416 mm)	28.75



54474

Slide-Rack Locking Bars

- Steel bars lock to secure mid-size storage boxes in slide racks.
- Front hasp pivots down to allow locking bar to open.
- Available for Klein four-box and six-box racks.
- Strong piano hinge.
- Metallic-grey baked-enamel finish.
- Mounting holes allow for easy installation with sheet metal screws or pop rivets.

Cat. No.	Description	Weight (lbs.)
54484	locking bar for Cat. No. 54474 slide rack	.25
54486	locking bar for Cat. Nos. 54476 & 54477 slide racks	.35



54484

Mid-Size Compartment Boxes

- Klein storage boxes are offered with a choice of compartment sizes and arrangements.
- Boxes feature strong, rigid, heavy-duty welded construction.
- Full-length piano hinged covers are designed to stay open for ease of access.
- Each box has a carrying handle, positive pull-down locking catch.
- Boxes have a heavy, metallic-gray baked-enamel finish.
- Box compartments feature high-impact styrene construction.
- Scoop-bottom design for easy parts removal and cleaning.
- Fits either four-drawer slide rack Cat. No. 54474 or six-drawer rack Cat. No. 54476.



54438

Cat. No.	Number of Compartments	Compartment Sizes	Length (Front to Back)	Width	Height	Weight (lbs.)
54436	8	6-7/16" x 2-1/16" (164 mm x 52 mm)	9-3/4" (248 mm)	13-5/16" (338 mm)	2" (51 mm)	3.90
54437	12	4-5/16" x 2-5/16" (110 mm x 59 mm)	9-3/4" (248 mm)	13-5/16" (338 mm)	2" (51 mm)	4.10
54438	16	3-1/4" x 2-5/16" (83 mm x 59 mm)	9-3/4" (248 mm)	13-5/16" (338 mm)	2" (51 mm)	4.40
54439	20	2-5/8" x 2-5/16" (67 mm x 59 mm)	9-3/4" (248 mm)	13-5/16" (338 mm)	2" (51 mm)	4.50
54440	21	20 each 2-1/16" x 2-5/16" (52 mm x 59 mm) and one 2-3/4" x 9-1/16" (70 mm x 230 mm)	9-3/4" (248 mm)	13-5/16" (338 mm)	2" (51 mm)	4.25

All dimensions are in inches and (millimeters).

