

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
 Class I, Zone 2, AEx nA IIC
 Class II, Division 1, Group E, F, G
 Class II, Division 2, Group F, G
 Class III







NEC/CEC:

Type 3R, 4, 4X
 IP66/67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water)

ATEX/IECEX:

Zone 2 and 22
 II 2 GD
 IP66/67

Mounting Hoods ①

	Description	Hub Size	Catalog Number NEC/CEC and ATEX/IEC
Pendant			
	One Hub, Rigid Mounting	3/4 1 M20	KPA-75 KPA-100 KPA-M20
Pendant Cone			
	One Hub, Rigid Mounting	3/4 1 M20	KPCH-75 KPCH-100 KPCH-M20
Ceiling			
	Five Hubs, Four Close-Up Plugs	3/4 1 M20	KPC-75 KPC-100 KPC-M20
Wall			
	Five Hubs, Four Close-Up Plugs	3/4 1 M20	KPWB-75 KPWB-100 KPWB-M20
25° Stanchion			
	One Hub	1-1/4 1-1/2	KPS-125 KPS-150
90° Stanchion			
	One Hub	1-1/4 1-1/2	KPST-125 KPST-150

Mercmaster LED Ballast and Mounting Hood Weights

Description	Weight kg (lb)
Fixture Unit (Ballast Housing)	8.8 (19.4)
Pendant Mounting Hood	1.0 (2.25)
Pendant Cone Mounting Hood	1.1 (2.50)
Ceiling Mounting Hood	1.4 (3.00)
Wall Mounting Hood	1.8 (4.00)
25° Stanchion Mounting Hood	1.5 (3.25)
90° Stanchion Mounting Hood	1.7 (3.75)

① For ATEX/IECEX rated fixtures, ballast bodies and mounting hoods must be purchased separately.