# WALL PLATES Specifications



#### **Application**

Legrand's broad line of Pass & Seymour<sup>®</sup> Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour devices.

#### **Thermoset Plastic Wall Plates**

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

#### TradeMaster<sup>®</sup> Thermoplastic Wall Plates

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

#### **Screwless Polycarbonate Wall Plates**

- Molded of .065" thick polycarbonate, matte finish.
- 2-piece plastic subplate made of polycarbonate.
- Extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond; and three metallic finishes.

#### **Metal Wall Plates**

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel.
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.


#### Materials

- Type 302/304 Stainless Steel, nonmagnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302/304, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates.
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.

## WALL PLATES

#### Dimensions

**[] legrand**®



#### **Standard Size Wall Plates**

- Standard size wall plates for all applications.
- Best fit for surface mount boxes.
- Available in plastic and metal only.

#### Dimensions

1 gang	2.75" x 4.5"
2 gang	4.56" x 4.5"
3 gang	6.375" x 4.5"
4 gang	8.125" x 4.5"
5 gang	10" x 4.5"
6 gang	11.812" x 4.5"
-	

- 7 gang 13.62" x 4.5"
- 8 gang 15.44" x 4.5"

#### TradeMaster® Wall Plates

- Extra 3/16" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and decorator single gang plates.

#### Dimensions

1 gang	2.9375" x 4.6875"
2 gang	4.75" x 4.6875"

3 gang	6.563" x 4.6875"

- 4 gang 8.375" x 4.6875"
- **5 gang** 10.188" x 4.6875"
- 6 gang 12" x 4.6875"

#### Screwless Polycarbonate Wall Plates

- Available in decorator openings.
- Extra 1/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.2-piece plastic subplate made of
  - polycarbonate
- Available in 3 metallic finishes and 6 standard colors.

#### Wall Plate Dimensions

1 gang	3.10" x 4.87"
2 gang	4.912" x 4.87"
3 gang	6.724" x 4.87"
4 gang	8.536" x 4.87"

#### **Subplate Dimensions**

- 1 gang
   2.85" x 4.62"

   2 gang
   4.662" x 4.62"

   3 gang
   6.474" x 4.62"
- 4 gang 8.286" x 4.62"

#### Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates.
- Additional coverage for sheet rock gaps.
- Available in plastic and metal only.

#### Dimensions

- 1 gang3.125" x 4.87"2 gang4.93" x 4.87"3 gang6.75" x 4.87"
- 4 gang 8.56" x 4.87"

#### TradeMaster<sup>®</sup> Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle, and decorator single gang plates.

#### Dimensions

1 gang	3.3125" x 5.0625"
2 gang	5.125" x 5.0625"
3 gang	6.9375" x 5.0625"
4 gang	8.75" x 5.0625"

#### Jumbo Wall Plates


- Extra 3/4" width and height than Standard size wall plates.
- Largest size wall plates to cover larger wall damage.
- Available in plastic and metal only.

#### Dimensions

1 gang	3.5" x 5.25"			
2 gang	5.31" x 5.25"			
3 gang	7.12" x 5.25"			
4 gang	8.93" x 5.25"			

# WALL PLATES

#### **Dimensions**




#### Sectional Wall Plates

End and center panels with each of five most-used configurations make it possible to improvise custom wall plates on the job. Panels lock securely together on installation. Blank sections furnished with mounting strap.


#### Wall Plate Mountings

Illustrated are the five standard methods of plate mounting. There are many other non-standard methods which depend upon the special device used. Exact mounting hole specifications for every device appear in the Selector Guide.




#### Wall Plate Sizes


#### Standard Size Available in plastic and metal









Junior-Jumbo




**TradeMaster Jumbo** Available in nylon only








#### **Tandem Wall Plates**



Metal only. Plate mounting dimensions are non-standard. Refer to Page P-26 for details and devices that can be used.

#### Screwless Wall Plate **Plastic Subplate**



For Screwless (SWP) Wall Plate dimensions refer to Page P-4.



### La legrand®

### WALL PLATES

### Communication Plates Standard Size Plastic & Metal

		NYLON	THERMOSET	METAL	
DESCRIPTION	COLOR	TRADEMASTER® PLATES	SMOOTH	MATERIAL	SMOOTH
TELEPHONE OR CABLE OUTLET	13/32" HOLE, BOX MOU	NTED	1		
• One Gang • 1 Outlet • [Metal plates have removable 13/32" I.D. grommet in 17/32" hole.]	lvory White Brown Gray Black Red Light Almond	TP11I TP11W TP11 TP11GRY TP11BK TP11RED TP11LA	SP11I SP11W SP11	Brass 302/304 S/S	SB11 SS11
<ul> <li>. Two Gang</li> <li>2 Outlets</li> <li></li> </ul>	lvory White Gray		SP21I SP21W SP21GRY	302/304 S/S	SS21
TELEPHONE OR CABLE OUTLET					
One Gang 1 Outlet, 1 #340 Yoke (Metal plates have removable 13/32" I.D. grommet in 17/32" hole.)	lvory White Brown Gray Black Red Light Almond	TP12I TP12W TP12 TP12GRY TP12BK TP12LA	SP12I SP12W SP12 SP12BK SP12RED SP12LA	Brass 430S/S 302/304 S/S	SB12 SL12 SS12
Two Gang 2 Oulets				302/304 S/S 302/304 S/S Painted Ivory 302/304 S/S Painted White 302/304 S/S Painted Gray	SS22 SS22I SS22W SS22GRY
TELEPHONE OR CABLE OUTLET	5/8" HOLE, STRAP MOL	INTED			
• One Gang 1 Outlet • 1 #340 Yoke (Metal plates have removable 13/32" I.D. grommet in 17/32" hole.]				302/304 S/S	SS730
TELEPHONE OR CABLE OUTLET	13/32" HOLE WITH KNO	CKOUT, STRAP MOUNTED			
One Gang 1 Outlet 1 #340 Yoke	lvory Brown Gray		SP732I SP732 SP732GRY		
TELEPHONE OR CABLE OUTLET	5/8" ID, BOX MOUNTED				
• One Gang ● 1 Outlet	lvory White Light Almond	TP60I TP60W TP60LA	SP60I SP60W SP60LA		
TELEPHONE OR CABLE OUTLET	1 1/4" HOLE, STRAP MO	DUNTED			
• One Gang 1 Outlet Supplied With #340 Yoke				302/304 S/S	SS736