POPULATING THE STRUCTURED MEDIA ENCLOSURE - THE NERVE CENTER OF THE CONNECTED HOME

Get enterprise-grade, best-in-class broadband network performance capability with Leviton Connected Home components. All Structured Media solutions are engineered to work together, providing a clean and organized base and simplifying integration from rough-in through line activation.

1

Structured Media Enclosures

These versatile enclosures allow you to manage and distribute a full range of voice, data, audio, and video wiring from one central location. We have enclosure solutions for wood frame, concrete, and cinder block construction.



Data Patching and Distribution

Leviton offers durable CAT 6 and 5e panels and modules for data cable distribution. The high-end Twist & Mount Panel makes installation easy and provides easy access for moves, additions, or changes in the home network.

3

Telephone Patching and Distribution

Choose from a wide selection of telephone distribution boards, modules, or panels for the secure feel and sound of a telephone landline. Our Telephone Input Distribution Panel (TIDP) supports inputs for use with "triple play" modems and complements the look and simplicity of our Twist & Mount Patch Panels.





MDU SYSTEMS | Populating the Structured Media® Enclosure



Internet Routers and Switches

Leviton has high-speed routers to share Internet access over a Wide Area Network (WAN) in the home or office, and Ethernet switches to network additional PCs, printers, and other peripherals beyond router capacity.



Ultra High-Flex Patch Cords

The structured cabling system you install today will likely change tomorrow. Ultra High-Flex Patch Cords help make changes easy. They allow for tighter radius connections and a cleaner finished appearance inside a dressed Structured Media Enclosure.





Premium and Passive CATV Splitters

Distribute the incoming RF signal to locations throughout a home via coaxial cable using Leviton's passive CATV splitters, or use Premium splitters to optimize the performance of digital cable signals to handle HDTV. The Premium splitter's forward-path internal amplifier provides equal input and output levels on all ports.





Integrated Power Supply

Structured cabling systems rely on active gear that requires low-voltage power and surge protection. Leviton offers power supplies with extra plugs that eliminate the need for bulky power adapters within enclosures.





Multi-Room Audio

The Hi-Fi 2 Four Source, Four Zone (4x4) is a quality distributed audio system that integrates easily inside a Structured Media enclosure. It is ideal for controlling, sharing, and listening to audio systems throughout the home. More information on the Hi-Fi 4x4 system is available online at leviton.com/hifi4x4.




ISP Modem (provided by service provider)

The modem converts DSL, cable, or fiber optic signals for Internet access for tripleplay service or pure data connections.



MDU | Data & A/V Connectors



DAI	A & A/V CONNECTORS		
DESCRIPTION		APPLICATIONS	PART NO.
	QuickPort® CAT 5 Connector	Voice and low-speed data	41108-R‡5
	QuickPort CAT 3 Connector	Voice and low-speed data	41108-R‡3
[A]	QuickPort GigaMax [®] CAT 5e Connector	High-speed data	5G108-R‡5
	QuickPort Voice-Grade 6-Conductor Connector	Voice	41106-R‡6
	QuickPort Voice-Grade 8-Conductor Connector	Voice	41108-R‡8
[B]	QuickPort BNC Bulkhead Module, standard	CCTV and video	41084-B*F
[C]	QuickPort BNC Bulkhead Module, gold plated	CCTV and video	40832-0B°
D]	QuickPort HDMI Passthrough	TV, DVD, satellite, and home theater	40834-00#
	QuickPort S-Video Feedthrough	Enhanced video streams	40734-CV~
E]	QuickPort USB A-A Connector, feedthrough	Computers and peripherals	40835-00~
[F]	QuickPort 3.5 mm Stereo, screw terminal	Computer audio	40839-S~S
[G]	QuickPort F-Connector, standard, 3.0 GHz	TV, DVD, satellite, and home theater	41084-F*F
[H]	QuickPort F-Connector, gold plated, 3.0 GHz	TV, DVD, satellite, and home theater	40831-0B°
	QuickPort RCA to 110	Advanced audio and video	40735-Rx+
	QuickPort RCA w/ black stripe	Advanced audio and video	40830-B*E
	QuickPort RCA w/ red stripe	Advanced audio and video	40830-B*R
	QuickPort RCA w/ yellow stripe^	Advanced audio and video	40830-B°Y
	QuickPort RCA w/ green stripe	Advanced audio and video	40830-B~V
	QuickPort RCA w/ blue stripe	Advanced audio and video	40830-B~L
	QuickPort Banana Jack Adapter, gold plated w/ black stripe	Advanced audio	40837-B°E
	QuickPort Banana Jack Adapter, gold plated w/ red stripe	Advanced audio	40837-B°R
[1]	QuickPort Binding Post Adapter, gold plated w/ black stripe	Advanced audio	40833-B°E
[J]	QuickPort Binding Post Adapter, gold plated w/ red stripe	Advanced audio	40833-B°R
	QuickPort Snap-in Blank Module	Secures unused ports	41084-B*B
[K]	QuickPort Compression RCA Connector	Advanced audio and video	40782-R•W
[L]	QuickPort Compression F-Connector (white only)	TV, DVD, satellite, and home theater	40782-CPF
[M]	RCA Compression Connector (colored rings included)	CCTV and video	40985-CRU
N]	Compression F-Connector	CCTV and video	40985-CPF
= Col = Inne = Col = Inne = Col = Colo = Colo	imum order quantity and lead times may apply. or: White (W), Ivory (I) er Barrel Color: Orange (O), Red (R), White (W), Yellow (Y) or: White (W), Light Almond (T), Ivory (I), Grey (G), Black (E) er Barrel Color: Black (E), Yellow (Y), Red (R), Blue (L), Green (V) or: Choose from any of the 1.3 colors shown at right. or: White (W), Light Almond (T), Ivory (I), Grey (G), Black (E), Brown (B) or: White (W), Light Almond (T), Ivory (I) or: White (W), Light Almond (T), Ivory (I), Black (E)	White (W) Light Almond (T) Ivory (I) Grey (G) Black (E) Yellow (Y) Orange (O) Crimson (C) Dark Red (R) Purple (P	Brown (B) Blue (L) Gree

MDU data & a/v connectors