

Device Boxes

Conduit Knockouts







O0	
"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in	Recessed ea

support bracket.





Cl3102-SSX	BC1104	CI1104-B	
"Wranground" bracket for 1-5/8 in steel stude With integral	Rangesad pare		




Cat. No	Volume (Cu. in.)	Features		Knockouts			
		Ears	Bracket	1/2 in. ends	1/2 in. bottom		
2 in. Deep — Gangable — 3 in. x 2 in							
CI425	10.0	flush	rework	2	-		
BC1102	10.0	recessed	-	2	-		
CI1102-SB	10.0	-	"SB"	2	-		
Cl3102-SSX	12.0	-	"SSX"	2	-		
2-1/2 in. Deep — Gangable — 3 in. x 2 in.							
BC1104	12.5	recessed	-	2	2		
CI1104-B	12.5	-	"B"	2	2		



347 V Boxes

HV (347 V) vs Regular Box Spacing



Extension Rings

