



BURNDY Catalog Number YAL34T58
UPC Number 78181041737
Description CANLUG-500KCML-SHORT-3/8
Status null

Web Use
BURNDY Product Line

Dimensional

Tongue Angle Straight
Length (in) 3.18
Tongue Type Standard
Barrell Style Chamfered
Bolt Hole Size (in) 0.66
Barrel Type Standard
Thickness 0.23
B Length (in) 1.37
Pad Width (in) 1.52

General

Number of Holes 1

Conductor(s)

Copper Stranded (Range) 500
Copper Solid Size (Range) N/A

Physical

Type of Plating Tin - Electro Plated
Color Code Brown
Plated (Yes or No) Y
Index Number 20
Product Material Copper

Approvals / Certifications

Industry Standards UL468A-468B
UL Listed Yes,Y
CSA Certified Yes,Y
ROHS Compatible Compliant
UL Recognized N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday
Phone: 800-346-4175